

Female cordset


9416



- Socket
- Straight
- 12-pin
- Right-rotating

Female cordset

Dimensions



Technical Data

General specifications

Number of pins	12-pin right-rotating
Construction type	straight
Connection 1	socket
Construction type 1	straight
Threading 1	M23

Ambient conditions

Pollution degree	3
------------------	---

Mechanical specifications

Connection type	Solder connection
Core cross section	0.08 ... 1 mm ²
Cable diameter	3 ... 10.5 mm
Degree of protection	IP67
Mass	76 g
Mating cycles	50

Release date: 2024-09-23 Date of issue: 2024-09-23 Filename: 103947_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com


USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 PEPPERL+FUCHS

Connection



Release date: 2024-09-23 Date of issue: 2024-09-23 Filename: 103947_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com