


## **Model Number**

## V1S-G-DUO-PG11

Field-attachable male connector, Duo version

### Features

- · Screw terminal connection
- Metal locking
- Simple assembling of 2 signals to one ٠ M12 plug-in station
- Two double cable seals included in • the delivery package
- Suitable for cable diameters ٠ 2 ... 3 mm und 4 ... 5 mm



# **Technical data**

Dimensions

General specifications	
Number of pins	4
Connection 1	Male connector
Construction type 1	straight
Threading 1	M12
UL File Number	E363587
Electrical specifications	
Operating voltage U	3 max. 250 V AC/DC
Operating current	max. 4 A
Volume resistance	< 8 mΩ
Ambient conditions	
Ambient temperature	-40 85 °C (-40 185 °F)
Pollution Degree	3
Mechanical specifications	
Degree of protection	IP67
Connection	1 x M12 connector, straight Screw terminals for max. 0.75 mm <sup>2</sup>
Material	
Contacts	CuZn
Contact surface	CuSnZn
Body	PA
Cable	
Sheath diameter	2.1 3 mm or 4 5 mm
Compliance with standards and directives	ec-
Standard conformity	
Degree of protection	EN 60529:2000
Electrical connection	



Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

