




Dimensions



Model number

WCS2-CS70-L1

Laminate type, 70 mm

Features

- Flexible installation by means of alu profile- or mounting bracket system
- High chemical resistance
- Low weight

Technical data

General specifications

Code rail height	a = 70 mm
Length	0.1 ... 327 m
Radius of bend	≥ 500 mm

Ambient conditions

Operating temperature	-40 ... 60 °C (-40 ... 140 °F)
Storage temperature	-40 ... 60 °C (-40 ... 140 °F)
Installation temperature	10 ... 60 °C (50 ... 140 °F)

Mechanical specifications

Material thickness	0.75 ... 0.95 mm
Tension loading	≤ 340 N
Material	polyester laminate
Thermal expansion coefficient	approx. 2.8×10^{-5} / K
Mass	40 g / m

Matching system components**WCS-MB**

Mounting bracket, straight

WCS-MB-C

Mounting bracket, straight

WCS-MB1

Mounting bracket for bolt connection, straight

WCS-MB2-C

Mounting bracket for C profile, straight section

WCS-MB2

Mounting bracket for C profile, straight section

WCS-MB2-UNI

Mounting bracket for UNISTRUT™ profile, straight section

WCS-MB-B

Mounting bracket, curve

WCS-MB1-B

Fastening angle for screw connection, curve

WCS-SP2

Stabilization profile

WCS-MB2-B-UNI

Mounting bracket for UNISTRUT™ profile, curved section

WCS-MB2-B

Mounting bracket for C profile, bend

Note

laminated version