

AS-Interface module mounting base U-G2FF-DIN


Fits on standard DIN rail

AS-Interface module mounting base for DIN Rail for connection to flat cable (AS-Interface and external auxiliary power)

Function

The base U-G2FF is used for connecting G2 modules in a long design to AS-Interface. For mounting, the module is snapped onto the DIN rail, the inserted flat cables are pressed into the contact prongs of the module and thus connected. For some modules, the connection to earth is established via this top part.

Dimensions



Technical Data

Ambient conditions	
Ambient temperature	-25 60 °C (-13 140 °F)
Storage temperature	-25 85 °C (-13 185 °F)
Mechanical specifications	
Degree of protection	IP67 according to EN 60529 (only in connection with module or cover)
Connection	AS-Interface flat cable
Material	
Housing	PBT
Dimensions	about 80, 45, 34 mm (L, W, H)

Connection

Do not connect inputs and outputs, which are supplied via the module from AS-interface or via auxiliary power, with power supply and signal circuits with external potentials.