



## **Model Number**

GLP30-RT/40b/103/123/143

Photoelectric slot sensor with 4-pin, M8 x 1 connector


## **Features**

- Plastic version •
- Clearly visible function indicators •
- External TEACH-IN •
- Degree of protection IP67


# **Product information**

An extremely favorable price/performance ratio and an innovative display concept characterize the GLP series. The switching states are visible from all directions. The optional attachment holes or dove tail joint significantly increase installation flexibility. The external, dynamic Teach-In function allows you to teach in moving objects easily.


**Dimensions** 



Туре	A	В	С	D	E	F		Number of mounting holes M4 *
GLP30-RT-	30	50	30	34	59.5	20	-	1
GLP50-RT-	50	70	50	54	79.5	20	28	2
GLP80-RT-	80	100	80	54	79.5	20	2 x 28	3
GLP120-RT-	120	140	120	54	79.5	20	3 x 28	4



#### **Electrical connection**






Pinout



### Indicators/operating means



1	Operating display	green
2	Signal display	yellow
3	TEACH-IN button	
4	Emitter	
5	Receiver	

Pepperl+Fuchs Group www.pepperl-fuchs.com

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com <sup>5</sup> PEPPERL+FUCHS 1

Technical data			Accessories		
General specifications			ОМН-К03		
Light source		LED , 640 nm pulsing	dove tail mounting clamp		
Light type		modulated visible red light	dovo kan mounting olamp		
Object size		min. 0.3 mm	V31-WM-2M-PUR		
Slot width		30 mm	Female cordset single-ended, M8, 4-pir		
Slot depth		34 mm	PUR cable		
Ambient light limit		10000 Lux			
ndicators/operating means			V31-GM-2M-PUR		
Function indicator		LED yellow , lit when the light beam is interrupted LED green: ready	Female cordset single-ended, M8, 4-pi PUR cable V31-GM-BK2M-PUR-U		
Control elements		Teach-In key , Sensitivity adjustment and Mode adjustment (NO/NC)			
Electrical specifications			Female cordset single-ended, M8, 4-pir		
Operating voltage U <sub>B</sub>		10 30 V DC	PUR cable		
Ripple		10 %			
No-load supply current	I <sub>0</sub>	≤ 30 mA	V31-WM-BK2M-PUR-U		
Input			Female cordset single-ended, M8, 4-pi		
Function input		external Teach-In	PUR cable		
Output					
Switching type		light/dark on	Other suitable accessories can be found www.pepperl-fuchs.com		
Signal output		1 PNP, short-circuit protected, reverse polarity protected, open collector			
Switching voltage		max. 30 V DC			
Switching current		max. 100 mA			
Voltage drop	U <sub>d</sub>	≤ 2.4 V			
Switching frequency	f	2000 Hz			
Response time		0.25 ms			
Conformity					
Product standard		EN 60947-5-2			
Ambient conditions					
Ambient temperature		-20 60 °C (-4 140 °F)			
Storage temperature		-20 80 °C (-4 176 °F)			
Mechanical specifications					
Degree of protection		IP67			
Connection		M8 connector, 4-pin			
Material					
Housing		PC			
Optical face		plastic			
Mass		20 g			
Approvals and certificates					
Protection class		II			
UL approval		cULus Listed, Class 2 Power Source "For use in NFPA 79 Applications only" Adapters providing field wiring means are available from the manufacturer. Refer to manufacturers information.			

2

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com