



Model Number

GLP80-RT/40b/103/156

Photoelectric slot sensor with 3-pin, M8 x 1 connector


Features

- Plastic version
- · Clearly visible function indicators
- Degree of protection IP67


Product information

An extremely favorable price/performance ratio and an innovative display concept characterize the GLP series. The switching states are visible from all directions. The optional attachment holes or dove tail joint significantly increase installation flexibility. The external, dynamic Teach-In function allows you to teach in moving objects easily.

Dimensions



Electrical connection



- O = Light on
- = Dark on


Pinout

Wire colors in accordance with EN 60947-5-2



BN (brown) BU (blue) BK (black)

Indicators/operating means



1	Operating display	green
2	Signal display	yellow
3	TEACH-IN button	
4	Emitter	
5	Receiver	

General specifications		
Light source		LED , 640 nm pulsing
Light type		modulated visible red light
Object size		min. 0.5 mm
Slot width		80 mm
Slot depth		54 mm
Ambient light limit		10000 Lux
Indicators/operating means		
Function indicator		LED yellow , lit when the light beam is interrupted LED green: ready
Control elements		Teach-In key , Sensitivity adjustment and Mode adjustment (NO/NC)
Electrical specifications		
Operating voltage	U_B	10 30 V DC
Ripple		10 %
No-load supply current	I ₀	≤ 30 mA
Output		
Switching type		light/dark on
Signal output		1 PNP, short-circuit protected, reverse polarity protected, open collector
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Voltage drop	U_d	≤ 2.4 V
Switching frequency	f	2000 Hz
Response time		0.25 ms
Conformity		
Product standard		EN 60947-5-2
Ambient conditions		
Ambient temperature		-20 60 °C (-4 140 °F)
Storage temperature		-20 80 °C (-4 176 °F)
Mechanical specifications		
Degree of protection		IP67
Connection		M8 connector, 3-pin
Material		
Housing		PC
Optical face		plastic
Mass		35 g
Approvals and certificates		
Protection class		II
UL approval		cULus Listed, Class 2 Power Source "For use in NFPA 79 Applications only" Adapters providing field wiring means are available from the manufacturer. Refer to manufacturers information.

Accessories

OMH-K03

dove tail mounting clamp

V3-WM-2M-PUR

Female cordset single-ended, M8, 3-pin, PUR cable

V3-GM-BK2M-PUR-U

Female cordset single-ended, M8, 3-pin, PUR cable

V3-WM-BK2M-PUR-U

Female cordset single-ended, M8, 3-pin, PUR cable

Other suitable accessories can be found at www.pepperl-fuchs.com

FPEPPERL+FUCHS