

Stack light solid light element VAZ-LAMP-70MM-RD

- Modular design
- Flexible combination of signal elements
- Bayonet system for simple mounting and dismounting
- 70-mm-series

Stack light solid light element, red











Function

The element lights using an incandescent, low-cost bulb. It has been designed and tested according to EN 60947-5-1. It is available in a variety of colors and is easy to fit into the corresponding connection element by means of a bayonet system. Its modular design permits any combinations and has reduced operating and storage costs.

Dimensions





Technical Data

General specifications		
UL File Number		E223176
Color		red
Electrical specifications		
Rated operating voltage	Ue	24 V AC/DC
Rated operating current	I_{e}	illuminant dependend
Protection class		III
Bulb		24 V / max. 7 W holder BA15D
Compliance with standards and directives		
Directive conformity		

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

EMC Directive 2004/108/EC

Standard conformity

Release date: 2022-08-29 Date of issue: 2022-08-29 Filename: 216076_eng.pdf

EN 60947-5-1 EN 60947-1

Technical Data Degree of protection EN 60529 Ambient conditions Ambient temperature -20 ... 60 °C (-4 ... 140 °F) Mechanical specifications Degree of protection IP65 Connection Bayonet system Life span illuminant dependend

Scope of Delivery

Bulbs are not included.

Matching System Components

VAZ-CLAMP-70MM	Stack light terminal base with cover plate
VAZ-CLAMP-70MM-90°	Stack light terminal base with cover plate

Accessories

	VAZ-LAMP-70MM- BULB-5W/24V	Bulb for solid light element stack light
--	-------------------------------	--