

# Stack light solid light element VAZ-LAMP-70MM-GN

- Modular design
- Flexible combination of signal elements
- Bayonet system for simple mounting and dismounting
- 70-mm-series

Stack light permanent light element, green









## **Function**

The element lights using an incandescent, low-cost bulb. It has been designed and tested according to EN 60947-5-1. It is available in a variety of colors and is easy to fit into the corresponding connection element by means of a bayonet system. Its modular design permits any combinations and has reduced operating and storage costs.

### **Dimensions**





### **Technical Data**

General specifications				
UL File Number		E223176		
Color		green		
Electrical specifications				
Rated operating voltage	U <sub>e</sub>	24 V AC/DC		
Rated operating current	l <sub>e</sub>	illuminant dependend		
Protection class		III		
Bulb		24 V / max. 7 W holder BA15D		
Compliance with standards and directives				
Directive conformity				
EMC Directive 2004/108/EC		EN 60947-5-1 EN 60947-1		

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Standard conformity

Release date: 2022-08-29 Date of issue: 2022-08-29 Filename: 216077\_eng.pdf

#### **Technical Data** Degree of protection EN 60529 **Ambient conditions** Ambient temperature -20 ... 60 °C (-4 ... 140 °F) **Mechanical specifications** Degree of protection IP65 Connection Bayonet system illuminant dependend Life span

# **Scope of Delivery**

Bulbs are not included.

# **Matching System Components**

VAZ-CLAMP-70MM	Stack light terminal base with cover plate
VAZ-CLAMP-70MM-90°	Stack light terminal base with cover plate

### **Accessories**

	VAZ-LAMP-70MM- BULB-5W/24V	Bulb for solid light element stack light
--	-------------------------------	--

**5**PEPPERL+FUCHS