

Stack light solid light element VAZ-LAMP-70MM-BU

- Modular design
- Flexible combination of signal elements
- Bayonet system for simple mounting and dismounting
- 70-mm-series

Stack light solid light element, blue











The element lights using an incandescent, low-cost bulb. It has been designed and tested according to EN 60947-5-1. It is available in a variety of colors and is easy to fit into the corresponding connection element by means of a bayonet system. Its modular design permits any combinations and has reduced operating and storage costs.

Dimensions





Technical Data

| General specifications | | |
|--|----------------|---------------------------------|
| UL File Number | | E223176 |
| Color | | blue |
| Electrical specifications | | |
| Rated operating voltage | U _e | 24 V AC/DC |
| Rated operating current | l _e | illuminant dependend |
| Protection class | | III |
| Bulb | | 24 V / max. 7 W holder BA15D |
| Compliance with standards and directives | | |
| Directive conformity | | |
| EMC Directive 2004/108/EC | | EN 60947-5-1 EN 60947-1 |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Standard conformity

Release date: 2022-08-29 Date of issue: 2022-08-29 Filename: 216080_eng.pdf

Technical Data Degree of protection EN 60529 Ambient conditions Ambient temperature -20 ... 60 °C (-4 ... 140 °F) Mechanical specifications Degree of protection IP65 Connection Bayonet system Life span illuminant dependend

Scope of Delivery

Bulbs are not included.

Matching System Components

| VAZ-CLAMP-70MM | Stack light terminal base with cover plate |
|--------------------|--|
| VAZ-CLAMP-70MM-90° | Stack light terminal base with cover plate |

Accessories

| | VAZ-LAMP-70MM- BULB-5W/24V | Bulb for solid light element stack light |
|--|-------------------------------|--|
|--|-------------------------------|--|