

Diffuse mode sensor ML100-8-W-200-RT/102/115b



- Miniature design
- Easy to use
- Very bright, highly visible light spot
- Full metal thread mounting
- Highly visible LEDs for Power ON and switching state
- Not sensitive to ambient light

Diffuse mode sensor with rectangular light spot for clear object detection, 200 mm detection range, red light, light/dark on, sensitivity adjuster, DC version, NPN output, fixed cable with M12 plug









Function

The optical sensors of this series are suitable for both standard and demanding applications. The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

Dimensions







Technical Data

| General specifications | |
|------------------------|---------------------------------|
| Detection range | 0 200 mm |
| Adjustment range | 15 200 mm |
| Reference target | standard white, 200 mm x 200 mm |

| Technical Data | | |
|--------------------------------------|----------------|---|
| Light source | | LED |
| Light type | | modulated visible red light |
| Polarization filter | | no |
| Diameter of the light spot | | approx. 170 mm at a distance of 200 mm |
| Optical face | | frontal |
| Ambient light limit | | EN 60947-5-2:2007+A1:2012 |
| Functional safety related parameters | | |
| MTTF _d | | 860 a |
| Mission Time (T _M) | | 20 a |
| Diagnostic Coverage (DC) | | 0 % |
| Indicators/operating means | | |
| Operation indicator | | LED green: power on |
| Function indicator | | LED yellow, lights up with receiver lit |
| Control elements | | sensitivity adjustment |
| Control elements | | Light-on/dark-on changeover switch |
| Electrical specifications | | |
| Operating voltage | U _B | 10 30 V DC |
| Ripple | - 5 | max. 10 % |
| No-load supply current | Io | <20 mA |
| Output | | |
| Switching type | | The switching type of the sensor is adjustable. The default setting is: light-on |
| Signal output | | 1 NPN output, short-circuit protected, reverse polarity protected, open collector |
| Switching voltage | | max. 30 V DC |
| Switching current | | max. 100 mA , resistive load |
| Voltage drop | U _d | ≤ 1.5 V DC |
| Switching frequency | f | 1000 Hz |
| Response time | | 0.5 ms |
| Conformity | | |
| Product standard | | EN 60947-5-2 |
| Approvals and certificates | | |
| UL approval | | cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure |
| CCC approval | | CCC approval / marking not required for products rated ≤36 V |
| Ambient conditions | | |
| Ambient temperature | | -30 60 °C (-22 140 °F) |
| Storage temperature | | -40 70 °C (-40 158 °F) |
| Mechanical specifications | | |
| Housing width | | 11 mm |
| Housing height | | 31 mm |
| Housing depth | | 20 mm |
| Degree of protection | | IP67 |
| Connection | | 300 mm fixed cable with 4-pin, M12 x 1 connector |
| Material | | |
| Housing | | PC (Polycarbonate) |
| Optical face | | PMMA |
| Mass | | approx. 20 g |
| Tightening torque, fastening screws | | 0.6 Nm |
| Cable length | | 0.3 m |



Connection




Connection Assignment



Wire colors in accordance with EN 60947-5-2


ΒN (brown) 2 WH (white) BU (blue) BK (black)

Assembly





| 1 | Light-Dark-switching | |
|---|----------------------|--------|
| 2 | Sensitivity adjuster | |
| 3 | Signal display | yellow |
| 4 | Operating display | green |

Characteristic Curve



Characteristic Curve





Accessories

| | OMH-ML100-09 | Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm |
|--|---------------|---|
| A STATE OF THE STA | OMH-ML100-01 | Mounting aid for ML100 series, mounting bracket |
| | OMH-ML100-02 | Mounting aid for ML100 series, mounting bracket |
| | OMH-ML100-03 | Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm |
| | OMH-ML100-04 | Mounting aid for ML100 series, mounting bracket |
| | OMH-ML100-05 | Mounting aid for ML100 series, mounting bracket |
| * | OMH-F10-ML100 | Mounting aid for ML100 series |
| | OMH-10 | Mounting aid for ML100 series |

Accessories OMH-ML100-S1 Mounting bracket V1-G-2M-PUR Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable grey V1-W-2M-PUR Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey