



# Stack light LED permanent light element

## VAZ-LED-40MM-CLD-GN

- Modular design
- Flexible combination of signal elements
- Bayonet system for simple mounting and dismounting
- Long lifetime
- 40-mm-series


Stack light LED permanent light element, green



### Function

The LED permanent light element converts electrical signals to optical signals. It has been designed and tested according to EN 60947-5-1. The light element is available in various colours and the bayonet type connector allows easy installation on the corresponding terminal. The modular design permits user-defined combinations and reduces operation costs and storage costs. The illuminant based on LED technology is integrated in the spherical cap and features an excellent illumination, good resistance against shock and vibration as well as a long service life.

### Dimensions



### Technical Data

General specifications			
Light type			LED
UL File Number			E223176
Color			green
Electrical specifications			
Rated operating voltage	U <sub>e</sub>	24 V	AC/DC
Protection class			II
Current consumption			35 mA
Inrush current			500 mA
Ambient conditions			
Ambient temperature			-30 ... 60 °C (-22 ... 140 °F)
Mechanical specifications			

Release date: 2022-06-30 Date of issue: 2022-06-30 Filename: 324824\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

**PF** PEPPERL+FUCHS

## Technical Data

Degree of protection	IP66
Connection	Bayonet system
Material	PC
Mass	28 g
Life span	max. 50,000 h

## Matching System Components

	<b>VAZ-CLAMP-40MM</b>	Stack light terminal base with cover plate
-----------------------------------------------------------------------------------	-----------------------	--------------------------------------------