



Stack light LED permanent light element

VAZ-LED-40MM-CLD-YE

- Modular design
- Flexible combination of signal elements
- Bayonet system for simple mounting and dismounting
- Long lifetime
- 40-mm-series


Stack light LED permanent light element, yellow



Function

The LED permanent light element converts electrical signals to optical signals. It has been designed and tested according to EN 60947-5-1. The light element is available in various colours and the bayonet type connector allows easy installation on the corresponding terminal. The modular design permits user-defined combinations and reduces operation costs and storage costs. The illuminant based on LED technology is integrated in the spherical cap and features an excellent illumination, good resistance against shock and vibration as well as a long service life.

Dimensions



Technical Data

General specifications

Light type	LED
UL File Number	E223176
Color	yellow

Electrical specifications

Rated operating voltage	U_e	24 V AC/DC
Protection class		II
Current consumption		35 mA
Inrush current		500 mA

Ambient conditions

Ambient temperature	-30 ... 60 °C (-22 ... 140 °F)
---------------------	--------------------------------

Mechanical specifications

Release date: 2022-06-30 Date of issue: 2022-06-30 Filename: 324825_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PF PEPPERL+FUCHS

Technical Data

Degree of protection	IP66
Connection	Bayonet system
Material	PC
Mass	28 g
Life span	max. 50,000 h

Matching System Components

	VAZ-CLAMP-40MM	Stack light terminal base with cover plate
---	-----------------------	--