

# Stack light LED permanent light element

### VAZ-LED-40MM-CLD-BU

- Modular design
- Flexible combination of signal elements
- Bayonet system for simple mounting and dismounting
- Long lifetime
- 40-mm-series


Stack light LED permanent light element, blue



### **Function**


The LED permanent light element converts electrical signals to optical signals. It has been designed and tested according to EN 60947-5-1. The light element is available in various colours and the bayonet type connector allows easy installation on the corresponding terminal. The modular design permits user-defined combinations and reduces operation costs and storage costs. The illuminant based on LED technology is integrated in the spherical cap and features an excellent illumination, good resistance against shock and vibration as well as a long service life.

#### **Dimensions**



#### **Technical Data**

General specifications		
Light type		LED
UL File Number		E223176
Color		blue
Electrical specifications		
Rated operating voltage	$U_e$	24 V AC/DC
Protection class		I
Current consumption		35 mA
Inrush current		500 mA
Ambient conditions		
Ambient temperature		-30 60 °C (-22 140 °F)
Mechanical specifications		



Release date: 2022-06-30 Date of issue: 2022-06-30 Filename: 324827\_eng.pdf

Technical Data				
Degree of protection	IP66			
Connection	Bayonet system			
Material	PC			
Mass	28 g			
Life span	max. 50,000 h			

## **Matching System Components**

VAZ-CLAMP-40MM	Stack light terminal base with cover plate