



Model Number

KHE-C01-2,2-2,0-K140

Plastic fiber optic - thru-beam

Features

- High flexible
- Side light outlet enables installation when space is at a premium

Description

Attention:

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



Technical data

General specifications

Detection range		SU18: 150 mm SU18/35: 600 mm SU19: 150 mm
Fiber optic length	l	2000 mm , adjustable
Fiber optic diameter	d	2.2 mm
Adapter form		00
End piece		Thread / cylindrical right angle
Bending radius		min. 2 mm
Fiber configuration	Fv	see dimensions
Angle of divergence		67 °
Accessories provided		Cutter for plastic fiber optics

Ambient conditions

Ambient temperature		-55 ... 70 °C (-67 ... 158 °F)
---------------------	--	--------------------------------

Mechanical specifications

Material		
Optical face		plastic
Sheathing		PVC
Core		plastic
End piece		brass, nickel-plated

Dimensions

