

- NOTES:
1. ALL DIMENSIONS IN MM.
 2. IN THE CASE OF HOLES WITH DIFFERENT DIAMETERS THE WORST CASE MUST BE CONSIDERED.
 3. ALL DISTANCES ARE MINIMUM SPACINGS
 4. MAXIMUM MATERIAL REMOVAL IS TOTAL AREA PERMITTED FOR EACH FACE CASE MUST BE CONSIDERED.
 5. THE INTERNAL GROUNDING TERMINAL SHALL BE USED AS THE PRIMARY EQUIPMENT GROUND. THE EXTERNAL TERMINAL IS ONLY A SUPPLEMENTAL BONDING CONNECTION WHERE LOCAL AUTHORITIES PERMIT OR REQUIRE SUCH A CONNECTION.

COVER - FIGURE 1				SIDES - FIGURE 2				BACK - FIGURE 3								
Dimension	H	H	H	G	MAX MATL REMOVAL (SQ MM)	D3	D3	D3	D2	D4	D1	MAX MATL REMOVAL (SQ MM)	D3	D3	D1	MAX MATL REMOVAL (SQ MM)
	HOLE TO HOLE						HOLE TO HOLE							HOLE TO HOLE		
	5 M20	M25	M32	ALL		5 M32	M50	M50	ALL	ALL	ALL		5 M32	M50	ALL	
	5 1/2"NPT	3/4"NPT	1"NPT	ALL		5 1"NPT	1.5"NPT	2"NPT	ALL	ALL	ALL		5 1"NPT	1.5"NPT	ALL	
EJ80	20	20	20	35	1118	20	30	30	15	15	25	804	30	45	25	981
EJ84	20	20	20	35	6431	20	30	30	15	20	25	3925	30	45	25	1608
EJ88A	25	30	30	40	4019	20	30	30	15	20	25	7715	30	45	25	2412
EJ88B	25	30	30	40	4019	20	30	30	15	20	25	7850	30	45	25	2412
EJ810A	25	30	30	50	6431	20	30	30	15	25	25	3925	30	45	25	3925
EJ810B	25	30	30	50	6431	20	30	30	15	25	25	5888	30	45	25	3925
EJ811A	25	30	30	50	11254	20	30	30	15	25	25	11640	30	45	25	3925
EJ811B	25	30	30	50	11254	20	30	30	15	25	25	5888	30	45	25	3925
EJ815A	25	30	30	60	16077	20	30	30	15	25	25	7715	30	45	25	3925
EJ817Q	50	60	60	60	19292	30	45	45	15	30	25	3925	30	45	25	3925
EJ818A	50	60	60	65	19292	30	45	45	15	30	25	9813	30	45	25	5888
EJ818B	50	60	60	65	19292	30	45	45	15	30	35	9813	30	45	35	5888




FIGURE 1




FIGURE 2




FIGURE 3

STAINLESS STEEL

COVER - FIGURE 1				SIDES - FIGURE 2				BACK - FIGURE 3								
Dimension	H	H	H	G	MAX MATL REMOVAL (SQ MM)	D3	D3	D3	D2	D4	D1	MAX MATL REMOVAL (SQ MM)	D3	D3	D1	MAX MATL REMOVAL (SQ MM)
	HOLE TO HOLE						HOLE TO HOLE							HOLE TO HOLE		
	5 M20	M25	M32	ALL		5 M32	M50	M63	M75	ALL	ALL		5 M32	M50	ALL	
	5 1/2"NPT	3/4"NPT	1"NPT	ALL		5 1"NPT	1.5"NPT	2"NPT	2.5"NPT	ALL	ALL		5 1"NPT	1.5"NPT	ALL	
EJ80	20	20	20	10	1608	20	30	30	45	15	15	804	20	30	30	981
EJ83A	20	30	30	10	2412	20	30	30	45	15	20	1963	20	30	30	981
EJ83A	20	30	30	10	2412	20	30	30	45	15	20	1963	20	30	30	981
EJ84A	20	30	30	10	7235	20	30	30	45	15	20	3116	20	30	30	1608
EJ86A	20	30	30	10	4823	20	30	30	45	15	20	1963	20	30	30	1472
EJ86A	25	30	30	10	9646	20	30	30	45	15	20	7850	20	30	30	2412
EJ88B	25	30	30	10	9646	20	30	30	45	15	20	9813	20	30	30	2412
EJ810A	25	30	30	10	8842	20	30	30	45	15	25	5888	20	30	30	2412
EJ810B	25	30	30	10	8842	20	30	30	45	15	25	5888	20	30	30	2412
EJ811A	25	30	30	10	14469	20	30	30	45	15	25	13247	20	30	30	3925
EJ811B	25	30	30	10	14469	20	30	30	45	15	25	13247	20	30	30	3925
EJ815A	25	30	30	10	20096	20	30	30	45	15	25	14719	20	30	30	3925
EJ817Q	25	30	30	10	19292	20	30	30	45	15	25	8831	20	30	30	3925
EJ818A	25	30	30	10	25723	20	30	30	45	15	25	22078	20	30	30	5888
EJ818B	25	30	30	10	25723	20	30	30	45	15	25	26494	20	30	30	5888