

Bestellbezeichnung / Model Number

VBA-*E*A-G10-Z*

VBA-*E-G10-Z*

VBA-*A-G10-E*



Elektrische Daten / Electrical specification

Bemessungsbetriebsspannung U_e ≤ 32 V PELV
Rated operating voltage U_e

Bemessungsbetriebsstrom I_e	VBA-*E1A-G10-ZAL*	≤ 60 mA
Rated operating current I_e	VBA-2E2A-G10-Z/*	≤ 200 mA
	VBA-2E-G10-Z*	≤ 120 mA
	VBA-*E-G10-Z*V31*	≤ 60 mA
	VBA-2A-G10-E*	≤ 60 mA
	VBA-4A-G10-E*	≤ 150 mA

Mechanische Daten / Mechanical specification

Anzugsdrehmoment / Tightening torque

Befestigungsschraube / Fastening screw 1,65 Nm / 1.65 Nm

Kabelverschraubung / Cable gland 0,4 Nm / 0.4 Nm

Umgebungsbedingungen / Ambient conditions

Umgebungstemperatur VBA-* -25 ... 65 °C / -13 ... 149 °F
Ambient temperature









Lagertemperatur VBA-* -25 ... 85 °C / -13 ... 185 °F
Storage temperature

Zulassungen und Zertifikate / Approvals and certificates

UL-Zulassung / UL approval cULus Listed, Type 1 enclosure

UL File Number E223772
„For use in NFPA 79 Applications only“

UL-anerkannte Flachkabel von P+F / UL recognized flat cable from P+F

Bestell- bezeichnung Order code	Farbe Color	Material	Aderquerschnitt Cross-section	UL cable style	Zulassungen Approvals
VAZ-FK-R-YE*	gelb/ yellow	TPE	2 x 1.5 mm ²	2103	CE  
VAZ-FK-R-BK*	schwarz/ black	TPE	2 x 1.5 mm ²	2103	CE  
VAZ-FK-PUR-YE*	gelb/ yellow	PUR	2 x 1.5 mm ²	20549	CE  
VAZ-FK-PUR-BK*	schwarz/ black	PUR	2 x 1.5 mm ²	20549	CE  
			2 x 2.5 mm ²	21866	

