



Product Service

CERTIFICATE

No. Z10 020068 0082 Rev. 00

Parameters:	Power supply:	24VDC -15%/+25%
	Nominal current:	max. 250mA
	I max. of the OSSD (s. instruction manual)	
	- for solid state output:	0.5A
	- for relay output:	2A
	Degree of protection:	IP65
	Operating temperature:	0°C to +55°C
	Detection capability:	50mm
	Operating distance:	SLPC(C)(M)8-2A: 0.2-8m SLPC(C)(M)10: 0.2-10m SLPC(C)(M)30: 6-30m SLPC(C)(M)65: 12-65m

Tested according to: EN ISO 13849-1:2015 (Cat. 4, PL e)
EN 61496-1:2013 (Type 4)
IEC 61496-2:2013 (Type 4)

Factory(ies): 063390, 062019, 104943

Model(s): **Safety light curtain:**
SLPC8-2A, SLPC10, SLPC30, SLPC65,
SLPCC8-2A, SLPCC10, SLPCC30, SLPCC65,
SLPCM8-2A, SLPCM10, SLPCM30, SLPCM65