



中国国家强制性产品认证证书



证书编号：2021322316003614

认证委托人名称： Pepperl+Fuchs SE
 认证委托人地址： Lilienthalstraße 200, 68307 Mannheim, Germany
 生产者名称： Pepperl+Fuchs SE
 生产者地址： Lilienthalstraße 200, 68307 Mannheim, Germany
 生产企业名称： Pepperl+Fuchs Asia Pte. Ltd.
 企业地址： 18 Ayer Rajah Crescent, Singapore 139942

产品名称： 隔离式安全栅
 系列、规格、型号： HiC2025ES, HiD2025ES
 标准： GB/T 3836.1-2021、GB/T 3836.4-2021

认证模式：型式试验+初始工厂检查+获证后监督

上述产品符合 CNCA-C23-01:2019 《强制性产品认证实施规则 防爆电气》的要求，特发此证。产品相关信息详见附件。

发证日期：2023年03月28日

有效期至：2026年01月04日

首次发证日期：2021年01月05日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询



批准：



上海仪器仪表自控系统检验测试所有限公司

<http://www.sitiias.com.cn>

中国·上海·漕宝路103号200233

电话：+86 21 64510844

S 0008799



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION



CERTIFICATE NO: 2021322316003614

APPLICANT: Pepperl+Fuchs SE
ADDRESS: Lilienthalstraße 200, 68307 Mannheim,Germany
MANUFACTURER: Pepperl+Fuchs SE
ADDRESS: Lilienthalstraße 200, 68307 Mannheim,Germany
FACTORY: Pepperl+Fuchs Asia Pte. Ltd.
ADDRESS: 18 Ayer Rajah Crescent, Singapore 139942

PRODUCT: Isolated Barrier
SERIES,SPECIFICATION,MODEL: HiC2025ES, HiD2025ES
STANDARDS: GB/T 3836.1-2021、GB/T 3836.4-2021

Type of Certification: Type test + Initial inspection + Surveillance inspection

This is to certify that the above mentioned product(s)complies with the requirements of implementation rules for compulsory certification (REFNO. CNCA-C23-01:2019). Refer to the attachment for detailed information.

Valid from:March 28, 2023

Valid until:January 4, 2026

Date of original certification:January 5, 2021

The validity of this certificate is subject to positive result of the periodic surveillance by issuing certification body until the expiry date.

This certificate is available through CNCA’s website: www.cnca.gov.cn



APPROVAL:

Guo AiHua



Shanghai Inspection and Testing Institute of Instruments and Automation Systems Co., Ltd.

<http://www.sitiias.com.cn>

Building 9,103 Cao Bao Road, Shanghai 200233,China

Tel: +86 21 64510844

S 0007073



中国国家强制性产品认证证书



证书编号: 2021322316003614

附件

产品名称: 隔离式安全栅

型号规格: HiC2025ES, HiD2025ES

防爆标志: [Ex ia Ga] IIC
[Ex ia Da] IIIC

电气参数: 非本安端子(连接件 SL1) 电气参数:

插脚代号	最高电压 Um	额定参数 Un
1a, 1b(-); 2a, 2b(+)	253Vac	24 Vdc (19~30 Vdc)
6b	253Vac	30 Vdc
8a(+); 7a(-)	253Vac	30 Vdc

本安端子(连接件 SL2) 电气参数(线性输出):

插脚代号	最高输出电压 Uo (V)	最大输出电流 Io (mA)	最大输出功率 Po (mW)	最大等效内部参数	
				Ci (nF)	Li (mH)
5a(+), 5b(-)	25.2	100	630	5.7	0

组别	最大外部参数		
	Co (μF)	Lo (mH)	Lo/Ro (μH/Ω)
IIC	0.1	3.5	55
II B/IIIC	0.81	14	222
II A	2.8	28	174

批准:



上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书



证书编号：2021322316003614

附 件

插脚代号	最高输出电压 U_o (V)	最大输出电流 I_o (mA)	最大输出功率 P_o (mW)	最大等效内部参数	
				C_i (nF)	L_i (mH)
5a(+), ; 1b(-), 7a(-)	7.2	100	25	5.7	0

插脚代号	最高输入电压 U_i (V)	最大输入电流 I_i (mA)
5a(+), 1b(-), 7a(-)	30	128

组 别	最大外部参数		
	C_o (μ F)	L_o (mH)	L_o/R_o (μ H/ Ω)
II C	13.49	3.5	27
II B/IIIC	239	14	108
II A	1000	28	216

相关报告编号： 2023S17402-011342

使用条件：

- 特殊（限制）使用条件：
 - 产品使用环境温度范围为 $-20^{\circ}\text{C} \sim +70^{\circ}\text{C}$ 。
 - 该产品只能与已获认证的Pepperl+Fuchs的HiC或HiD系列端子板一起使用。

批 准：



上海仪器仪表自控系统检验测试所有限公司