

## EU-Konformitätserklärung

Pepperl+Fuchs SE  
Lilienthalstraße 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No. / Nr.: DOC-0193D  
Date / Datum: 2022-03-23

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



### Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives and standards**.

Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien und Normen** entsprechen.

### Products / Produkte

Product / Produkt	Item number	Description / Beschreibung
F2-SP-ICX	238250-YYYY	Segment Protector in IP66 aluminium housing

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

### Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
ATEX 2014/34/EU (L96/309-356)	EN 60079-11:2012-01 EN 60079-15:2010-05 EN 60079-31:2014-07 EN IEC 60079-0/AC:2020-02 EN IEC 60079-0:2018-07
EMC 2014/30/EU (L96/79-106)	EN 61326-1:2013-01
RoHS 2011/65/EU (L174/88-110)	EN IEC 63000:2018-12

### Affixed CE Marking / Angebrachte CE-Kennzeichnung



### Signatures / Unterschriften

Mannheim, 2022-03-23

ppa. Michael Kessler

Executive Vice President Components & Technology

i.V. Norbert Lindner

i.V. Norbert Lindner  
Continuation Manager Value Engineering

### ANNEX ATEX

**Notified Body QM-System** / Notifizierte Stelle des QM-Systems  
Physikalisch Technische Bundesanstalt (0102)  
Bundesallee 100  
38116 Braunschweig  
Germany

### Marking and Certificates / Kennzeichnung und Zertifikate

Marking Kennzeichnung	Certificate Zertifikat	Issuer ID Aussteller ID
 	TÜV 13 ATEX 107689X	TUN

### Key for Issuer ID / Schlüssel zur Aussteller ID

ID	Issuer / Aussteller
TUN	TÜV NORD CERT GmbH Langemarckstraße 20 45141 Essen Germany

Pepperl+Fuchs SE declares that the products are only affected by minor or formal changes with respect to the new edition of the standards. These changes are not relevant for compliance with the essential health and safety requirements. The products still comply with the ATEX Directive. This declaration is also valid if the marking and the certificates of the listed devices correspond to previous editions of standards.

Die Pepperl+Fuchs SE erklärt hiermit, dass die Produkte nur von kleineren oder formalen Änderungen in Bezug auf die neue Ausgabe der Normen betroffen sind. Diese Änderungen sind nicht relevant für die Konformität mit den wesentlichen Gesundheits- und Sicherheitsanforderungen. Die Produkte erfüllen nach wie vor die ATEX-Richtlinie. Diese Erklärung gilt auch, wenn die Kennzeichnung und die Zertifikate der aufgeführten Geräte vorangegangenen Normenständen entsprechen.

Product family type code description:

**Type Code/Order Designation**

**Type of housing**

**F2** Field housing, aluminum, IP65

**Function**

**SP** Segment Protector

**Explosion protection method**

**IC** Ex ic, non-incendive field wiring rated spur outputs

**Number of outputs**

**04** 4 spurs

**06** 6 spurs

**08** 8 spurs

**10** 10 spurs

**Terminal options**

**0** Screw terminal, non-pluggable

**1** Screw terminal, pluggable

**2** Spring terminal

**Trunk cable entry options**

**00** M20 stopping plug, plastic

**01** M20 stopping plug, stainless steel

**02** M20 cable gland, plastic

**03** M20 cable gland, nickel plated brass

**04** M20 cable gland, stainless steel

**05** M20 cable gland, nickel plated brass for armored cable

**06** M20 cable gland, stainless steel for armored cable

**09** M12 plug connection, nickel plated brass FOUNDATION Fieldbus

**10** M12 plug connection, nickel plated brass PROFIBUS PA

**11** M12 plug connection, stainless steel FOUNDATION Fieldbus

**12** M12 plug connection, stainless steel PROFIBUS PA

**Spur cable entry options**

**00** M20 stopping plug, plastic

**01** M20 stopping plug, stainless steel

**02** M20 cable gland, plastic

**03** M20 cable gland, nickel plated brass

**04** M20 cable gland, stainless steel

**05** M20 cable gland, nickel plated brass for armored cable

**06** M20 cable gland, stainless steel for armored cable

**09** M12 plug connection, nickel plated brass FOUNDATION Fieldbus

**10** M12 plug connection, nickel plated brass PROFIBUS PA

**11** M12 plug connection, stainless steel FOUNDATION Fieldbus

**12** M12 plug connection, stainless steel PROFIBUS PA

**Accessory options**

**0** No tag plate

**1** Tag plate stainless steel incl. printing

**2** Tag plate stainless steel excl. printing

**0** No trunk surge protector

**1** Trunk surge protector

F2	-	SP	-	IC		.		.		.		.	
A	-	B	-	C	D	.	E	.	F	.	G	.	H I