

Pepperl+Fuchs SE
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / Nr.: DOC-4429A
Date / Datum: 2021-10-25

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.

Product family / Produktfamilie

Product / Produkt	Description / Beschreibung
DT4S-a-dM-e-DT4P-f-g	Extension cable Deutsch connector to Deutsch connector 4-pin

The "a", "d", "e", "f" and "g" marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit "a", "d", "e", "f" und "g" markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
2011/65/EU (RoHS) (L174/88-110)	EN IEC 63000:2018-12

Affixed CE Marking / Angebrachte CE-Kennzeichnung



Signatures / Unterschriften

Mannheim, 2021-10-25

i.V. Sebastian Stöber
Director Business Unit SYSTEMS

i.V. Simon Wagner
Product Manager

ANNEX TYPE CODE

The "a", "d", "e", "f" and "g" marked letters of the type code are placeholders and can be replaced by the following code:

Die mit "a", "d", "e", "f" und "g" markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

DT4S-a-dM-e-DT4P-f-g	
DT4S DT4P	Connector type
a, f	G = Straight; W = Angled
d	Color (blank = Grey; BK = Black; BL = Blue; BN = Brown; GN = Green; YE = Yellow; OR = Orange; RD = Red; VT = Violet; WT = White) + length in m
e	Jacket Material (PUR; PVC; PUR-U; PUR-U/ABG; PUR-U5/ABG; PVC-U; PUR-U/0,75; PUR-ABG; PVC-ABG; PUR-A; PUR-R1; PUR-R2; PUR-R3; PUR-O1; PUR-O2; PUR-O3; POC; PUR-O1S; PUR-O2S; PUR-O3S; TPE; PP; PUR-E1, PUR-E2; PUR-E3; PUR-E1S; PUR-E2S; PUR-E3S)
g	blank = Standard; Y followed by any number = Special version