

Pepperl+Fuchs SE  
Lilienthalstraße 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No. / Nr.: DOC-4430A  
Date / Datum: 2021-10-25

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



**Declaration of conformity / Konformitätserklärung**

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.

**Product family / Produktfamilie**

Product / Produkt	Description / Beschreibung
DT6S-a-dM-e-g	Female cord set Deutsch connector 6-pin

The "a", "d", "e" and "g" marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit "a", "d", "e" und "g" markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

**Directives and Standards / Richtlinien und Normen**

EU-Directive EU-Richtlinie	Standards Normen
2011/65/EU (RoHS) (L174/88-110)	EN IEC 63000:2018-12

**Affixed CE Marking / Angebrachte CE-Kennzeichnung**



**Signatures / Unterschriften**

Mannheim, 2021-10-25

i.V. Sebastian Stöber  
Director Business Unit SYSTEMS

i.V. Simon Wagner  
Product Manager

**ANNEX TYPE CODE**

The "a", "d", "e" and "g" marked letters of the type code are placeholders and can be replaced by the following code:

Die mit "a", "d", "e" und "g" markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

DT6S-a-dM-e-g	
DT6S	Connector type
a	G = Straight; W = Angled
d	Color (blank = Grey; BK = Black; BL = Blue; BN = Brown; GN = Green; YE = Yellow; OR = Orange; RD = Red; VT = Violet; WT = White) + length in m
e	Jacket Material (PUR; PVC; PUR-U; PUR-U/ABG; PUR-U5/ABG; PVC-U; PUR-U/0,75; PUR-ABG; PVC-ABG; PUR-A; PUR-R1; PUR-R2; PUR-R3; PUR-O1; PUR-O2; PUR-O3; POC; PUR-O1S; PUR-O2S; PUR-O3S; TPE; PP; PUR-E1, PUR-E2; PUR-E3; PUR-E1S; PUR-E2S; PUR-E3S)
g	blank = Standard; Y followed by any number = Special version