

Pepperl+Fuchs SE  
Lilienthalstraße 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No. / Nr.: DOC-4436A  
Date / Datum: 2021-10-21

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



### Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.

### Product family / Produktfamilie

Product / Produkt	Description / Beschreibung
V3-a-c-dM-e-V11-f-g	Connecting cable, M8 to M12

The "a", "c", "d", "e", "f" and "g" marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit „a“, „c“, „d“, „e“, „f“ und „g“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

### Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
2011/65/EU (RoHS) (L174/88-110)	EN IEC 63000:2018-12

Supplemental Standards Sonstige Normen	Remarks Bemerkungen
IEC 61076-2-101:2012	Connectors for electronic equipment - Product requirements - Part 2-101: Circular connectors - Detail specification for M12 connectors with screw-locking
IEC 61076-2-104:2014	Connectors for electronic equipment - Product requirements - Part 2-104: Circular connectors - Detail specification for M8 connectors with screw- and snap-locking

### Affixed CE Marking / Angebrachte CE-Kennzeichnung



### Signatures / Unterschriften

Mannheim, 2021-10-21

i.V.

i.V. Sebastian Stöber  
Director Business Unit SYSTEMS

i.V.

i.V. Simon Wagner  
Product Manager

### ANNEX TYPE CODE

The "a", "c", "d", "e", "f" and "g" marked letters of the type code are placeholders and can be replaced by the following code:

Die mit „a“, „c“, „d“, „e“, „f“ und „g“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

V3-a-c-dM-e-V11-f-g	
V3 V11	Connector type
a, f	GM=Straight metal nut; WM=Angled metal nut; GV4A=Straight stainless steel nut, WV4A= Angled stainless steel nut; GR= Snap Straight; WR=Snap angled
c	blank = Standard; N = Namur, 2-pole; N4 = Namur, 4-pole; GN = Green connector head; GY = Grey connector head; S = Safety, Yellow connector head; 41 = Pin 1 and Pin 4 are crossed; 42 = Pin 2 and Pin 4 are crossed; B = Bridged
d	Color (blank = Grey; BK = Black; BL = Blue; BN = Brown; GN = Green; YE = Yellow; OR = Orange; RD = Red; VT = Violet; WT = White) + length in m
e	Jacket Material (PUR; PVC; PUR-U; PUR-U/ABG; PUR-U5/ABG; PVC-U; PUR-U/0,75; PUR-ABG; PVC-ABG; PUR-A; PUR-R1; PUR-R2; PUR-R3; PUR-O1; PUR-O2; PUR-O3; POC; PUR-O1S; PUR-O2S; PUR-O3S; TPE; PP; PUR-E1, PUR-E2; PUR-E3; PUR-E1S; PUR-E2S; PUR-E3S)
g	blank = standard; Y followed by any number = special version