




Mannheim, 2021-10-19

Pepperl+Fuchs SE
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / Nr.: DOC-5381
Date / Datum: 2021-10-19

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com




i.V. Roof Wessels

Executive Vice President Business Unit
MCC+HMI


i.V. Jörg Hartleb

COO ECOM Instruments GmbH

■ Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.



Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.

■ Products / Produkte

Product / Produkt	Item number	Description / Beschreibung
Tab-Ex 03 Z2 WWAN	70144929	TAB-EX03-Z2--WWANEUR- CN-000-..
Tab-Ex 03 Z2 WWAN	70144928	TAB-EX03-Z2--WWANEUR- CS-000-..

■ ANNEX ATEX

Marking and Certificates / Kennzeichnung und Zertifikate

Marking Kennzeichnung	Certificate Zertifikat	Issuer ID Aussteller ID
 II 3 D  II 3 G	PF21CERT6297X	PF

Key for Issuer ID / Schlüssel zur Aussteller ID

ID	Issuer / Aussteller
PF	Pepperl+Fuchs Lilienthalstrasse 200 68307 Mannheim Germany

■ Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
ATEX 2014/34/EU (L96/309-356)	EN IEC 60079-0:2018-07 EN 60079-11:2012-01
RE 2014/53/EU (L153/62-106)	EN 300328 V 2.2.2:2019-07 EN 300330 V 2.1.1:2017-02 EN 300440 V 2.1.1:2017-03 EN 301489-1 V 2.2.3:2019-11 EN 301489-3 V 2.1.1:2019-03 EN 301489-17 V 3.1.1:2017-02 EN 301489-19 V 2.1.1:2019-04 EN 301489-52 V 1.1.0:2016-11 EN 301511 V 12.5.1:2017-03 EN 301893 V 2.1.1:2017-05 EN 301908-1 V 13.1.1:2019-11 EN 301908-2 V 13.1.1:2020-06 EN 301908-13 V 13.1.1:2019-11 EN 303413 V 1.1.1:2017-06 EN 50360:2017-10 EN 50566:2017-10 EN 50663:2017-10 EN 55035:2017-07 EN 62311:2008-01 EN IEC 62368-1:2020-03 EN IEC 62368-1/A11:2020-03 EN IEC 62368-3:2020-03
RoHS 2011/65/EU (L174/88-110)	EN IEC 63000:2018-12