

Pepperl+Fuchs SE
Lilienthalstrasse 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No: DOC-5862
Date: 2022-05-03

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

Product family

| Product | Description |
|----------------|----------------------------|
| V11-a-c-dM-e-g | Female cordset, M12, 3-pin |

The "a", "c", "d", "e" and "g" marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Regulations and Standards

| UK Regulation | Standards |
|----------------------------|----------------------|
| UK SI 2012 No. 3032 (RoHS) | EN IEC 63000:2018-12 |
| UK SI 2016 No. 1101 (LV) | EN 61010-1:2010-10 |

Affixed UKCA Marking



Signatures

Mannheim, 2022-05-03

i.V. Sebastian Stöber
Executive Vice President Business
Unit Systems

i.V. Wolfram Warnecke
Approval Engineer

ANNEX TYPE CODE

The "a", "c", "d", "e" and "g" marked letters of the type code are placeholders and can be replaced by the following code:

| V11-a-c-dM-e-g | |
|----------------|--|
| V11 | Connector type |
| a | G = Straight; W = Angled; GV4A = Straight stainless steel nut; WV4A = Angled stainless steel nut; GU = Straight Ultralock; WU = Angled Ultralock; GT = Straight Teflon; WT = Angled Teflon; GX = Straight XXL head, WX = Angled XXL head |
| c | Blank = Standard; GN = Green connector head; GY = Grey connector head; S = Safety, Yellow connector head; B = Bridged |
| d | Color (blank = Grey; BK = Black; BL = Blue; BN = Brown; GN = Green; YE = Yellow; OR = Orange; RD = Red; VT = Violet; WT = White) + length in m |
| e | Jacket Material (PUR; PVC; PUR-U; PUR-U/ABG; PUR-U5/ABG; PVC-U; PUR-U/0,75; PUR-ABG; PVC-ABG; PUR-A; PUR-R1; PUR-R2; PUR-R3; PUR-O1; PUR-O2; PUR-O3; POC; PUR-O1S; PUR-O2S; PUR-O3S; TPE; PP; PUR-E1, PUR-E2; PUR-E3; PUR-E1S; PUR-E2S; PUR-E3S) |
| g | blank = Standard; Y followed by any number = Special version |