

Pepperl+Fuchs SE
 Lilienthalstrasse 200
 68307 Mannheim
 Germany
 Phone +49 621 776-0
 Fax +49 621 776-1000

No: DOC-5880
 Date: 2022-07-08

Copyright Pepperl+Fuchs
 www.pepperl-fuchs.com



Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

Product family

Product	Description
V15-a-c-dM-e-V15-f-g	Female cordset, 5-pin M12 connector

The “a”, “c”, “d”, “e”, “f” and “g” marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12

Supplemental Standards	Remarks
IEC 61076-2-101:2012	Connectors for electronic equipment - Product requirements - Part 2-101: Circular connectors - Detail specification for M12 connectors with screw-locking

Affixed UKCA Marking



Signatures

Mannheim, 2022-07-08

i.V. Sebastian Stöber
 Executive Vice President Business
 Unit Systems

i.V. Wolfram Warnecke
 Approval Engineer

ANNEX TYPE CODE

The “a”, “c”, “d”, “e”, “f” and “g” marked letters of the type code are placeholders and can be replaced by the following code:

V15-a-c-dM-e-V15-f-g	
V15	Connector type
a, f	G = Straight; W = Angled; GV4A = Straight stainless steel nut; WV4A = Angled stainless steel nut; GU = Straight Ultralock; WU = Angled Ultralock; GT = Straight Teflon; WT = Angled Teflon; GX = Straight XXL head, WX = Angled XXL head
c	Blank = Standard; N = Namur, 2-pole; N4 = Namur, 4-pole; GN = Green connector head; GY = Grey connector head; S = Safety, Yellow connector head; 41 = Pin 1 and Pin 4 are crossed; 42 = Pin2 and Pin 4 are crossed; B = Bridged
d	Color (blank = Grey; BK = Black; BL = Blue; BN = Brown; GN = Green; YE = Yellow; OR = Orange; RD = Red; VT = Violet; WT = White) + length in m
e	Jacket Material (PUR; PVC; PUR-U; PUR-U/ABG; PUR-U5/ABG; PVC-U; PUR-U/0,75; PUR-ABG; PVC-ABG; PUR-A; PUR-R1; PUR-R2; PUR-R3; PUR-O1; PUR-O2; PUR-O3; POC; PUR-O1S; PUR-O2S; PUR-O3S; TPE; PP; PUR-E1, PUR-E2; PUR-E3; PUR-E1S; PUR-E2S; PUR-E3S)
g	blank = Standard; Y followed by any number = Special version