

Pepperl+Fuchs SE  
Lilienthalstrasse 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No: DOC-6539  
Date: 2022-08-02

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



### Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

### Product family

Product	Description
V19SY-a-c-dM-e-g	Male cordset, 8-pin M12 connector

The "a", "c", "d", "e" and "g" marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

### Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12

Supplemental Standards	Remarks
IEC 61076-2-101:2012	Connectors for electronic equipment - Product requirements - Part 2-101: Circular connectors - Detail specification for M12 connectors with screw-locking

### Affixed UKCA Marking



### Signatures

Mannheim, 2022-08-02

i.V. Sebastian Stöber  
Executive Vice President Business  
Unit Systems

i.V. Wolfram Warnecke  
Approval Engineer

### ANNEX TYPE CODE

The "a", "c", "d", "e" and "g" marked letters of the type code are placeholders and can be replaced by the following code:

V19SY-a-c-dM-e-g	
V19SY	Connector type
a	G = Straight; W = Angled; GV4A = Straight stainless steel nut; WV4A = Angled stainless steel nut; GU = Straight Ultra-lock; WU = Angled Ultra-lock; GT = Straight Teflon; WT = Angled Teflon
c	Blank = Standard; N = Namur, 2-pole; N4 = Namur, 4-pole; GN = Green connector head; GY = Grey connector head; S = Safety, Yellow connector head; 41 = Pin 1 and Pin 4 are crossed; 42 = Pin2 and Pin 4 are crossed; B = Bridged, X = XXL Head
d	Color (blank = Grey; BK = Black; BL = Blue; BN = Brown; GN = Green; YE = Yellow; OR = Orange; RD = Red; VT = Violet; WT = White) + length in m
e	Jacket Material (PUR; PVC; PUR-U; PUR-U/ABG; PUR-U5/ABG; PVC-U; PUR-U/0,75; PUR-ABG; PVC-ABG; PUR-A; PUR-R1; PUR-R2; PUR-R3; PUR-O1; PUR-O2; PUR-O3; POC; PUR-O1S; PUR-O2S; PUR-O3S; TPE; PP; PUR-E1, PUR-E2; PUR-E3; PUR-E1S; PUR-E2S; PUR-E3S)
g	blank = Standard; Y followed by any number = Special version