

Pepperl+Fuchs SE  
 Lilienthalstrasse 200  
 68307 Mannheim  
 Germany  
 Phone +49 621 776-0  
 Fax +49 621 776-1000

No: DOC-6740  
 Date: 2022-09-08

Copyright Pepperl+Fuchs  
 www.pepperl-fuchs.com



**Declaration of conformity**

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

**Product family**

Product	Description
V31-a-c-dM-e-V1-f-g	Connecting cable, M8 to M12

The "a", "c", "d", "e", "f" and "g" marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

**Regulations and Standards**

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12

Supplemental Standards <i>Sonstige Normen</i>	Remarks <i>Bemerkungen</i>
IEC 61076-2-101:2012	Connectors for electronic equipment - Product requirements - Part 2-101: Circular connectors - Detail specification for M12 connectors with screw-locking
IEC 61076-2-104:2014	Connectors for electronic equipment - Product requirements - Part 2-104: Circular connectors - Detail specification for M8 connectors with screw- and snap-locking

**Affixed UKCA Marking**



**Signatures**

Mannheim, 2022-09-08

i.V. Sebastian Stöber  
 Executive Vice President Business  
 Unit Systems

i.V. Simon Wagner  
 Product Manager

**ANNEX TYPE CODE**

The "a", "c", "d", "e", "f" and "g" marked letters of the type code are placeholders and can be replaced by the following code:

V31-a-c-dM-e-V1-f-g	
V31 V1	Connector type
a, f	GM=Straight metal nut; WM=Angled metal nut; GV4A=Straight stainless steel nut, WV4A= Angled stainless steel nut; GR= Snap Straight; WR=Snap angled
c	blank = Standard; N = Namur, 2-pole; N4 = Namur, 4-pole; GN = Green connector head; GY = Grey connector head; S = Safety, Yellow connector head; 41 = Pin 1 and Pin 4 are crossed; 42 = Pin 2 and Pin 4 are crossed; B = Bridged
d	Color (blank = Grey; BK = Black; BL = Blue; BN = Brown; GN = Green; YE = Yellow; OR = Orange; RD = Red; VT = Violet; WT = White) + length in m
e	Jacket Material (PUR; PVC; PUR-U; PUR-U/ABG; PUR-U5/ABG; PVC-U; PUR-U/0,75; PUR-ABG; PVC-ABG; PUR-A; PUR-R1; PUR-R2; PUR-R3; PUR-O1; PUR-O2; PUR-O3; POC; PUR-O1S; PUR-O2S; PUR-O3S; TPE; PP; PUR-E1, PUR-E2; PUR-E3; PUR-E1S; PUR-E2S; PUR-E3S)
g	blank = Standard; Y followed by any number = Special version