

Pepperl+Fuchs SE
 Lilienthalstrasse 200
 68307 Mannheim
 Germany
 Phone +49 621 776-0
 Fax +49 621 776-1000

No: DOC-6828
 Date: 2022-09-21

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

Product family

Product	Description
V15-a-b-c-d	M12 female A-coded 5-pin field attachable connector

The “a”, “b”, “c” and “d” marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12

Supplemental Standards	Remarks
IEC 61076-2-101:2012	Connectors for electronic equipment - Product requirements - Part 2-101: Circular connectors - Detail specification for M12 connectors with screw-locking

Affixed UKCA Marking



Signatures

Mannheim, 2022-09-21

i.V. Sebastian Stöber
 Executive Vice President Business
 Unit Systems

i.V. Simon Wagner
 Product Manager

ANNEX TYPE CODE

The “a”, “b” and “c” marked letters of the type code are placeholders and can be replaced by the following code:

V15-a-b-c-d	
V15	Connector type
a	G = Straight; W = Angled; GV4A = Straight stainless steel nut; WV4A = Angled stainless steel nut
b	ABG = Shielded; PG7 = 4-6mm sheath diameter; PG9 = 5-8mm sheath diameter; PG11 = 8-10mm sheath diameter
c	PG9 = 5-8mm sheath diameter; PG11 = 8-10mm sheath diameter
d	blank = Standard; Y followed by any number = Special version