

Pepperl+Fuchs SE  
Lilienthalstrasse 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No: DOC-6829  
Date: 2022-09-20

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



### Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

### Product family

Product	Description
V15S-a-b-c	M12 male A-coded 5-pin field attachable connector

The "a", "b" and "c" marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

### Regulations and Standards

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12

Supplemental Standards	Remarks
IEC 61076-2-101:2012	Connectors for electronic equipment - Product requirements - Part 2-101: Circular connectors - Detail specification for M12 connectors with screw-locking

### Affixed UKCA Marking



### Signatures

Mannheim, 2022-09-20

i.V. Sebastian Stöber  
Executive Vice President Business  
Unit Systems

i.V. Simon Wagner  
Product Manager

### ANNEX TYPE CODE

The "a", "b" and "c" marked letters of the type code are placeholders and can be replaced by the following code:

V15S-a-b-c	
V15S	Connector type
a	G = Straight; W = Angled; GV4A = Straight stainless steel nut; WV4A = Angled stainless steel nut
b	ABG = Shielded; PG7 = 4-6mm sheath diameter; PG9 = 5-8mm sheath diameter; PG11 = 8-10mm sheath diameter
c	PG9 = 5-8mm sheath diameter; PG11 = 8-10mm sheath diameter