

Pepperl+Fuchs SE  
 Lilienthalstrasse 200  
 68307 Mannheim  
 Germany  
 Phone +49 621 776-0  
 Fax +49 621 776-1000

No: DOC-6893  
 Date: 2022-11-18

Copyright Pepperl+Fuchs  
 www.pepperl-fuchs.com



**Declaration of conformity**

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** as indicated below and amended by **UK SI 2019 No. 696**, and **standards**.

**Product family**

Product	Description
V3-a-d-e-b-V1-f-g	Y-Splitter cordset

The “a”, “b”, “d”, “e”, “f” and “g” marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

**Regulations and Standards**

UK Regulation	Standards
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018-12

Supplemental Standards	Remarks
EN 61076-2-101:2012	Connectors for electronic equipment - Product requirements - Part 2-101: Circular connectors - Detail specification for M12 connectors with screw-locking
EN 61076-2-104:2014	Connectors for electronic equipment - Product requirements - Part 2-104: Circular connectors - Detail specification for circular connectors with M8 screw-locking or snap-locking

**Affixed UKCA Marking**



**Signatures**

Mannheim, 2022-11-18

i.V. Sebastian Stöber  
 Vice President Business Unit Systems

i.V. Simon Wagner  
 Product Manager

**ANNEX TYPE CODE**

The “a”, “b”, “d”, “e”, “f” and “g” marked letters of the type code are placeholders and can be replaced by the following code:

V3-a-d-e-b-V1-f-g	
V3 V1	Connector type
a	GM = Straight metal nut; WM = Angled metal nut; GV4A = Straight stainless steel nut, WV4A = Angled stainless steel nut; GR = Snap Straight; WR = Snap angled
b	TEE = T-Splitter with 1:1 wiring; YEE = Y-Splitter with 1:1 wiring; Y24B = Y-Splitter pin 2 and 4 bridged; YAND = Y-Splitter with AND wiring; Y = Y-Splitter; Y-TQ= Splitterbody with two holes
d	Color (blank = Grey; BK = Black; BU = Blue; BN = Brown; GN = Green; YE = Yellow; OR = Orange; RD = Red; VT = Violet; WT = White) + length in m
e	Jacket Material (PUR; PVC; PUR-U; PVC-U; PUR-U/0,75; PUR-A; PUR-R1; PUR-R2; PUR-R3; PUR-O1; PUR-O2; PUR-O3; POC; TPE; PP)
f	G = Straight; W = Angled; GV4A = Straight stainless steel nut; WV4A = Angled stainless steel nut
g	blank = Standard; Y followed by any number = Special version