

Pepperl+Fuchs SE  
Lilienthalstrasse 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No. : DOC-7150  
Date : 2023-01-03

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



### Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** and **standards**.

### Product family

Product family	Description
A**58*-*****_****	Absolute Encoder

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

### Regulations and Standards

UK Regulation	Standards
UK SI 2016 No. 1091 (EMC)	EN 61000-6-4:2019-02 EN 61000-6-2:2019-09
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018

### Affixed UKCA Marking



### Signatures

Mannheim, 2023-01-03

i.V. Stefan Horvatic  
Innovation Unit Manager Encoders

i.V. Christian Güntert  
Manager Product Management Encoders

**ANNEX TYPE CODE**

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:

Product Family	Housing material		Shaft Dimension	Flange	Connection type	Exit position	Option 1	Output code	Option 2		Number of bits multi turn	Number of bits single turn
<b>A**58</b>	*	-	**	*	**	*	*	*	*	-	**	**
ASS58 ASM58 AVS58 AVM58 AHS58 AHM58	N, I, W	-	01,02, 03, 05, 08, F1, F2, F3, F5, F6, F7, 0A, 0B	1, 2, A	K1, K2, K3, K4, K5, KA, KB, KC, AA, AB, BE	R, A	K, 0, H	B, G	N	-	12, 14	12,13,14,15 ,16