

Pepperl+Fuchs SE  
Lilienthalstrasse 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No.: DOC-7159  
Date : 2023-01-04

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



### ■ Declaration of conformity

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **UK Regulations** and **standards**.

### ■ Product family

Product family	Description
ENA58IL_*****_*****_***	Absolute Encoder

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

### ■ Regulations and Standards

UK Regulation	Standards
UK SI 2016 No. 1091 (EMC)	EN 61000-6-4:2019-02 EN 61000-6-2:2019-09
UK SI 2012 No. 3032 (RoHS)	EN IEC 63000:2018

### ■ Affixed UKCA Marking



### ■ Signatures

Mannheim, 2023-01-04

i.V. Stefan Horvatic  
Innovation Unit Manager Encoders

i.V. Christian Güntert  
Manager Product Management Encoders

**■ ANNEX TYPE CODE**

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:

Product Family		Shaft type	Shaft diameter	Flange	Protection class		Multiturn resolution	Singleturn resolution	Interface		Con-nection	Con-nection type
ENA58IL	-	*	**	**	*	-	**	**	***	-	*	**
	-	S; R; H	06; 08; 10; 11; 12; 14; 15; U1; U2; U3; U4; U5	SA, CA; QA; DA;	5; 7		00, 12, 13, 14, 15, 16	12, 13, 14, 16	SG1, SB1, SG2, SB2, SI1, SI2, SI3, SI4, SI5, SI6, SI7, SI8, SI9, SIA, SIB, SIC, B03; B06; B07; B12; B16, B17; B20, B21; B25; BCG, BJG, U01, U05, U04, U09, I42, I02; BM6; IO	-	A, R	C1, C2,C3,C 5, C6; C7; C8;C9;C A, KB, KC, KD, KE, KF, KG, KH, KJ, KK, KL, KM, KN BE,BD; AA; AB; AC; BP; BN; MA; MB; D1; H1; H2; H3; H4; H5