EU-Declaration of conformity

EU-Konformitätserklärung

en/de

Pepperl+Fuchs SE
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / *Nr.*: DOC-7678E
Date / *Datum*: 2025-10-27

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com

PEPPERL+FUCHS

Declaration of conformity / *Konformitätserklärung*

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

*Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.*

Productfamily / *Produktfamilie*

Productfamily / *Produktfamilie*	**Description** / *Beschreibung*
BTC24-XX-XXXX-XXX	Industrial Box Thin Client

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

Directives and Standards / *Richtlinien und Normen*

EU-Directive *EU-Richtlinie*	**Standards** *Normen*
2014/30/EU (EMC) (L96/79-106)	EN 61326-1:2021 EN 55032:2015+A11:2020+A1: 2020 EN 5011:2016+A1:2017+A11:2020+A2:2021 (Group 1, Class B)
2011/65/EU (RoHS) (L174/88-110)	EN IEC 63000:2018-12
(EU) 2023/1542 (L191/1-84)	EN IEC 63000:2018-12

Supplemental Standards *Sonstige Normen*	**Remarks** *Bemerkungen*
UL 61010-1:2023 UL 61010-2-201:2022	Low Voltage Directive

Affixed CE Marking / *Angebrachte CE-Kennzeichnung*

CE

Signatures / *Unterschriften*

Mannheim, 2025-10-27

i.V. Roolf Wessels
Executive Vice President
ECOM+HMI

i.V. Predrag Bursac
Continuation Manager HMI
Business Unit HMI

ANNEX TYPE CODE

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:
Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

BTC24-XX-XXXX-XXX			
Variable	**Feature**	**Option**	**Description**
BTC24-	Model	BTC24-	Industrial Box Thin Client
X	Certification	N	CE & FCC + UL Ordinary Location
X-	Operating Temperature	A-	Standard operating temperature
		B-	Extended operating temperature
X	Computing Platform	1	Intel Atom x6413E
X	RAM	A	8GB Standard Temperature RAM
		K	8GB Extended Temperature RAM
X	Storage	A	64 GB SSD
X-	Software	1-	VisuNet RM Shell 6 based on Windows 10 IoT LTSC
		J-	IGEL OS 12
		T-	ThinManager Ready
		X-	Other software options, X replaced by other alphanumerical character
XXX	Expansion	NN0	None