



Mannheim, 2024-10-18

i.V. Rolf Wessels
Executive Vice President
ECOM+HMIi.V. Lukas Polzin
Head of Value Engineering
Business Unit HMIPepperl+Fuchs SE
Lilienthalstrasse 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000No. / Nr.: DOC-7755
Date / Datum: 2024-10-18Copyright Pepperl+Fuchs
www.pepperl-fuchs.com

■ Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

*Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.*

■ Product Family / Produktfamilie

Product Family / Produktfamilie	Item number / Artikelnr.	Description / Beschreibung
EXTA4-N1-XX-XXXXX -XXXXX-XX-XX	70178585-*	Industrial Keyboard & Mouse

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

■ Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
2014/30/EU (EMC) (L96/79-106)	EN 61000-6-4:2019 EN IEC 61326-1:2021 (Industrial Locations)
2011/65/EU (RoHS) (L174/88-110)	EN IEC 63000:2018

■ ANNEX TYPE CODE

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

EXTA4-XX-XX-XXXXX-XXXXX-XX-XX			
Variable	Feature	Option	Description
EXTA4-	Technology	EXTA4-	Industrial Keyboard & Mouse
XX-	Certification	N1-	Industrial, Non-Ex version
XX-	Housing	NN-	no housing, panel mounting
		F1-	Standard housing with mounting options (bead blasted finish)
		F2-	Standard housing with mounting options (brushed finish)
		T1-	Desktop housing
XX	Mouse	K4	Capacitive Touchpad
		K6	Joystick
		K8	Optical Trackball
XXX-	Layout	US0-	US-International Layout
		DE0-	German Layout
		FR0-	French Layout
		XXX-	<i>other layout options, without impact on compliance</i>
XXX	Cable Length	U10	1 m
		U20	2 m
		U50	5 m
XX-	Connector	C1-	Cable ends with crimped ferrules
		U1-	1x USB type A male connector
XX-	Mounting	NP-	Panel mounting (w/o housing)
		NF-	Flush mounting (w/o housing)
		T1-	Desktop housing without mounting option
		G1-	One-Arm installation to VisuNet GXP in AG-XX00 housing
		G2-	Double-Arm installation to VisuNet GXP in AG1 housing
		H1-	Hinge for installation to VisuNet FLX in AG-320S housing
		C1-	Cabinet / horizontal installation on a vertical housing (Wall mounting)
XX	Options	N0	Standard
		U0	UV-resistant front foil