

## EU-Konformitätserklärung

Pepperl+Fuchs SE  
Lilienthalstraße 200  
68307 Mannheim  
Germany  
Phone +49 621 776-0  
Fax +49 621 776-1000

No. / Nr.: DOC-B010D  
Date / Datum: 2021-11-17

Copyright Pepperl+Fuchs  
www.pepperl-fuchs.com



### Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.

### Productfamily / Produktfamilie

Productfamily / Produktfamilie	Description / Beschreibung
VisuNet IND DM5XX Series	Industrial Flat Panel Monitors

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist

### Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
2014/30/EU (EMC) (L96/79-106)	EN 61326-1:2013
2011/65/EU (RoHS) (L174/88-110)	EN IEC 63000:2018

### Affixed CE Marking / Angebrachte CE-Kennzeichnung



### Signatures / Unterschriften

Mannheim, 2021-11-17

i.V. Roolf Wessels  
Executive Vice President  
Business Unit MCC+HMI

i.V. Lukas Polzin  
Manager Value Engineering  
Innovation Unit HMI

## ■ ANNEX TYPE CODE

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

DM5XX-XX-XX-XX-XX			
Variable	Description	Option	Description / Designation
XX	Screen Size	10 12 15 19 21 22	10.4", SVGA (800 x 600 pixel) 12.1" SVGA (800 x 600 pixel) 15.0", XGA (1024 x 768 pixel) 19.0", SXGA (1280 x 1024 pixel) 21.5", Full HD (1920 x 1080 pixel) 22.0", WSXGA (1680 x 1050 pixel)
X	Screen Type	T0 TA TH A0 N0	Resistive Touchscreen Resistive Touchscreen with Antiglare Hardened Resistive Touchscreen with Antiglare Antiglare, No Touchscreen Clear glass front, no Touchscreen
XX	Protection	GP GL	General Purpose General Purpose, LED Backlit
XXX	Housing Version	SS EN RM CM OM N0 SL NL EL	Stainless Steel, panel mount Enclosed Black Painted Steel, 19" Rackmount Chassis Mount OEM Black painted Steel bezel, panel mount Stainless Steel, panel mount, No Logo Black Painted Steel bezel, panel mount, No Logo Enclosed, No Logo
X	Options	NT PT HB NH PH N0	NTSC Input Special Drop-In replacement (18" and 19" only) LED backlight, High Brightness (12", 15", 19" only) NTSC Input, LED backlight, High Brightness (12", 15", 19" only) Special Drop-In replacement, LED Backlight, High Brightness (19" only) No Option