



■ Signatures / Unterschriften

Mannheim, 2018-07-18

i.V. Roolf Wessels
Business Unit Director

i.V. Nils Bleshoy
Norm Expert of the Product Group

■ ANNEX TYPE CODE

The „X“ marked letters of the type code are placeholders and can be replaced by the following code:

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



■ Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs GmbH declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

Die Pepperl+Fuchs GmbH erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien** und **Normen** entsprechen.

■ Productfamily / Produktfamilie

Productfamily / Produktfamilie	Description / Beschreibung
VisuNet IND-8200 Series	Direct -, Remote-, KVM Monitor and Panel PC

The „X“ marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit „X“ markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

■ Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
2014/30/EU (EMC) (L96/79-106)	EN 61326-1:2013
2011/65/EU (RoHS) (L174/88-110)	EN 50581:2012

XXXXXX-X-XX-XX-XX-XXX-X-XX-XX-XX-XX-X				
Variable	Description	Option	Description / Designation	
XXXX	Family	DM82 RM82 KM82 PC82	Direct Monitor Family Remote Monitor Family KVM Monitor Family Panel PC Family	
XX	Screen Size	15 19 21 22	15.0", XGA (1024 x 768 pixel) 19.0", SXGA (1280 x 1024 pixel) 21.5", Full HD (1920 x 1080 pixel) 22.0", WSXGA (1680 x 1050 pixel)	
X	Screen Type	A R T U F K	Antiglare glass front, non-touch Touch Screen, Resistive, 5-wire, hardened Glass (15", 19", 21.5" only) Touch Screen, Resistive, 5-wire High Bright Display with Touch Screen, Resistive, 5-wire (15", 19", 21.5" only) High Bright Display with antiglare front, non-touch (15", 19", 21.5" only) High Bright Display with Touch Screen, Resistive, 5-wire, hardened glass (15", 19", 21.5" only)	
XX	Protection	GP	General Purpose	
XX	Board Specification	V2	Video VGA	Only DM
		T3	Thin Client, ATOM 1.6 GHz, 1 GB RAM, 2GB Flash, RM shell (W7 based)	Only RM
		T4	Thin Client, ATOM 1.6 GHz, 2 GB RAM, 8GB Flash, W7 Embedded	Only RM
		TC	Thin Client, ATOM 1.6 GHz, 2GB RAM, Thin Manager Compliant	Only RM
		T51	Thin Client, ATOM Dual Core E3826, 4 GB RAM, 16GB CFAST, RM shell (W7 based)	Only RM
		T52	Thin Client, ATOM Dual Core E3826, 4 GB RAM, 16GB CFAST, W7 Embedded	Only RM
		T61	Thin Client, ATOM Dual Core E3826, 4 GB RAM, 32GB CFAST, RM Shell 5 (W10 IOT based)	Only RM
		K3	KVM for VGA Video included, 2x PS/2, 1x RS232, analogue CATx cable transmission, ROSE	Only KM
		K4	KVM for DVI-D Video included, 2 x USB, 1 x RS232, CATx cable transmission, ROSE	Only KM
		K5	KVM for DVI-D Video included, 2 x USB, 1 x RS232, F.O. transmission , 2x LC connectors, ROSE	Only KM
		PDX	i7 Dual Core processor, 4 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package)	Only PC
		PEX	i7 Dual Core processor, 8 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package)	Only PC
		PFX	ATOM Dual Core E3826, 4 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package)	Only PC
		PGX	ATOM Dual Core E3826, 8 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package)	Only PC
		PHX	ATOM Dual Core E3826, 4 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package)	Only PC
PIX	ATOM Dual Core E3826, 8 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package)	Only PC		
PJX	i7-7600U, 4 GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package)	Only PC		
PKx	i7-7600U, / GB RAM, 120 GB SSD, 4 x USB, 2 x Network, (X Determines Software Package)	Only PC		
XX	Power Supply	DC	24V DC	
XXX	Housing Version	CL5	Panel mount, stainless steel	
		CP5	Panel mount, black painted steel	
		CP6	19" Rack mount, black painted steel, Only 19" display	
X	Keyboard Housing	N	No Keyboard & Mouse housing	
XX	Keyboard / Mouse	K0	No Keyboard, no Mouse	
XX	Keyboard Layout	L0	No Keyboard, no Layout	
XX	Special Accessories	S0	No Special Accessories	
X	Options	N	No Option	