

EU-Konformitätserklärung

Pepperl+Fuchs SE
Lilienthalstraße 200
68307 Mannheim
Germany
Phone +49 621 776-0
Fax +49 621 776-1000

No. / Nr.: DOC-B0C4C
Date / Datum: 2022-05-15

Copyright Pepperl+Fuchs
www.pepperl-fuchs.com



Declaration of conformity / Konformitätserklärung

We, Pepperl+Fuchs SE declare under our sole responsibility that the **products** listed below are in conformity with the listed **European Directives** and **standards**.

Die Pepperl+Fuchs SE erklärt hiermit in alleiniger Verantwortung, dass die unten gelisteten **Produkte** den genannten **Europäischen Richtlinien und Normen** entsprechen.

Productfamily / Produktfamilie

Productfamily / Produktfamilie	Description / Beschreibung
7500-XX-XX-XXX-XXX-XXX	7500 zone 2/22 pressurization control system
EPV-7500-XX-XX	Enclosure protection vent for the 7500 pressurization control system
7500-MTD-XXXX-XX	7500 pressurization control system assembly for external or panel mounting.
7500-XXX-XX	7500 Hub Accessory
XXXX 30.1-00/ XXXX - XXXXXX	7500 Solenoid
AC10-U3-6-XXXX-XXXXXX	7500 Solenoid
AC10-U3-6-JJ04-JWXX-XXXX-XXXXXX	7500 Solenoid

The [X] marked letters of the type code are placeholders and can be replaced by the code described in ANNEX TYPE CODE.

Die mit [X] markierten Stellen im Typenschlüssel sind Platzhalter und können durch den Schlüssel ersetzt werden der in ANNEX TYPE CODE beschrieben ist.

Directives and Standards / Richtlinien und Normen

EU-Directive EU-Richtlinie	Standards Normen
EMC 2014/30/EU (L96/79-106)	EN 61326-1:2013
ATEX 2014/34/EU (L96/309-356)	EN IEC 60079-0:2018 EN 60079-2:2014 EN IEC 60079-7:2015 + A1:2018 EN IEC 60079-15:2019 EN 60079-18:2015 + A1:2017 EN 60079-31:2014
RoHS 2011/65/EU (L174/88-110)	EN IEC 63000:2018
Supplemental Standards Sonstige Normen	Remarks Bemerkungen
EN 61010-1:2010 + A1:2019 + A1/AC:2019-04	

Affixed CE Marking / Angebrachte CE-Kennzeichnung



Signatures / Unterschriften

Mannheim, 2022-05-15

i.V. Roolf Wessels
Business Unit Director

i.V. Brent Dean
Product Portfolio Manager – Purge
and Pressurization

ANNEX ATEX

Marking and Certificates / Kennzeichnung und Zertifikate

Marking Kennzeichnung	Certificate Zertifikat	Issuer ID Aussteller ID
 	DEMKO 18 ATEX 2025X	UL

Key for Issuer ID / Schlüssel zur Aussteller ID

ID	Issuer / Aussteller
UL	UL International Demko A/S Borupvang 5A 2750 Ballerup Denmark

TYPE CODE

The [X] marked letters of the type code are placeholders and can be replaced by the following code:

Die mit [X] markierten Stellen im Typenschlüssel sind Platzhalter und können durch folgenden Schlüssel ersetzt werden:

7500-xx-xx-xxx-xxx-xxx					
7500-	XX	XX	XXX	XXX	XXX
Standard pressurization control unit	01- max sensor pressure 5" WC 02- max sensor pressure 10" WC 03-max sensor pressure 10" WC XX -	Housing Material AA - Aluminum SS – 304 or 316SS	Mounting Configuration STD – Standard XXX -	Power Requirement UNV – Universal AC/DC XXX -	Wire Entrance Fittings PNO – M12 plug, only XXX -

Example: 7500-01-AA-STD-UNV-PNO

EPV-7500-xx-xx-xx			
EPV-7500	XX	XX	XX
Enclosure protection vent family for 7500	Housing material AA – Aluminum SS – Aluminum body, Stainless steel cap	Valve Configuration 01 – standard valve 02 – standard valve, lower leakage 03 – sealing type (AA and SS versions only) 04 – sealing type (AA version only)	Options BLANK – XX -

Example: EPV-7500-AA-01

7500-xxx-xxxx-xx			
7500	XXX	XXXX	XX
7500 mounted control system	Style MTD-Mounted XXX -	Configuration PMSW – square panel mount with control unit and manifold PMRW – rectangular panel mount with control unit and manifold BXSX – square box mount with control unit and manifold BXRW – rectangular box mount with control unit and manifold	Options 01– standard XX -

Example: 7500-MTD-PMSW-01

7500-xxx-xx		
7500	XXX	XX
7500 optional HUB	Style HUB- HUB accessory	Options 01– standard XX -

Example: 7500-HUB-01

xxxx 30.1-00/ xxxx - xxxxxx			
XXXX	30.1-00/	XXXX	XXXXXX
Coil Voltage Type 0515-AC-rated coil 1215-DC rated coil		Coil Code 6896 – 24VDC Coil, T5 6897 – 110VAC Coil, T5 6961 – 230VAC Coil, T5	Voltage Rating 024VDC 110VAC 230VAC

AC10-U3-6-XXXX-XXXXXX		
AC10-U3-6	XXXX	XXXXXX
Solenoid Family	Coil Code PX23 – T4, 40mm width coil, 9W PX26 – T6, 40mm width coil, 1.8W	Voltage Rating 024VDC (only for PX26) 110VAC 230VAC

AC10-U3-6-JJ04-JWXX-XXXX-XXXXXX			
AC10-U3-6-JJ04	JWXX	XXXX	XXXXXX
Solenoid Family	Cable Length: XX are any two alphanumeric characters that denote the length of the cable	Coil Code PX58 – T4, 40mm width coil, 9W PX61 – T6, 40mm width coil, 1.8W	Voltage Rating 024VDC (only for PX61) 110VAC 230VAC