



guía de luz de fibra óptica de reflexión con revestimiento PVC

Technical drawing of a shaft-hub assembly. The drawing shows a shaft of diameter d passing through a hub. The shaft has a section of length l that is free of the hub. The hub has an outer diameter of $\phi 4.5$ and an inner bore of $\phi 15$. The hub has a total length of 21, with a section of length 5 at the end. The shaft has a section of length 35, with a section of length 20 at the end. The shaft is secured with an M8 x 1 screw. The drawing includes dimension lines and arrows indicating the various lengths and diameters.

Grado de protección	IP65
---------------------	------

Datos técnicos

Material		
Salida de luz		Vidrio
Revestimiento		PVC
Núcleo		Fibra de vidrio
Pieza terminal		Acero inoxidable 1.4305 / AISI 303
Adaptador		PBT
Potencia extractora		100 N
Fibras ópticas		
Series de los aparatos		VL18LL VariKont M

Aplicación

Atención:

El conductor de luz no debe torcerse ni doblarse. Las fuerzas de tracción extremas pueden provocar deterioros. Evite el contacto con gasolina o disolventes orgánicos.

