



Model number

VAZ-9VDC-CHRG-115VAC

Power Supply

Features

- Replacement 110V power supply for all VBP-HH1* handheld programmers
- For use in North and South America

Technical data

Electrical specifications

Supply frequency		60 Hz
Nominal voltage	U_n	120 V
Current loading capacity		20 mA

Output

Current	100 mA
Voltage	9 V +/- 5%

Mechanical specifications

Protection degree	IP20
Connection	Power supply for AS-Interface Handheld programming device Supply voltage: 5.5 mm hollow socket
Material	
Mass	approx. 135 g
Cable length	1.8 m