

Power Rail

PR-03

- Alternative power supply
- Nominal current 4 A
- Simple installation
- Standard length 50 cm, can be shortened to any length in 4 cm steps
- Terminating insulation by end cap, included in the delivery package
- With 2 leads for voltage supply and 1 lead for centralized error messages


Power Rail with grid, 3 leads



Function

The Power Rail is a simple plastic insert for the DIN mounting rail according to EN 60715. It solves all of the power supply wiring problems involved when mounting terminal blocks. A wide range of isolators is available. These are supplied with auxiliary power by simply snapping them onto the Power Rail. The power supply to the 2 Power Rail leads is achieved either by means of a power supply module, or via the terminal blocks of a termination board. By comparison, the isolator power supply connections are only suitable for the supply of the individual modules. They are not suitable for the supply of the Power Rail or to further conduct the Power Rail voltage. The Power Rail is supplied in 50 cm sections. It can be cut every 4 cm along its length, at the positions indicated, to suit individual requirements. Gold plated contacts are provided to ensure secure electrical contact. Please use the standard type UPR-03 for new systems.

Assembly



Technical Data

Electrical specifications

Rated voltage	U_r	24 V DC
Rated current	I_r	4 A

Ambient conditions

Ambient temperature	-20 ... 60 °C (-4 ... 140 °F)
---------------------	-------------------------------

Release date: 2020-09-23 Date of issue: 2020-09-23 Filename: 119264_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com