



### Model Number

NCN4-12GM50-WS-V11

### Features

- Comfort series
- 4 mm non-flush

### Accessories

#### BF 12

Mounting flange, 12 mm

#### EXG-12

Quick mounting bracket with dead stop

## Technical Data

### General specifications

Switching element function		AC	NO
Rated operating distance	$s_n$	4 mm	
Installation		non-flush	
Output polarity		AC	
Assured operating distance	$s_a$	0 ... 3.24 mm	
Reduction factor $r_{Al}$		0.45	
Reduction factor $r_{Cu}$		0.4	
Reduction factor $r_{304}$		0.8	

### Nominal ratings

Operating voltage	$U_B$	20 ... 253 V
Switching frequency	$f$	0 ... 25 Hz
Voltage drop	$U_d$	$\leq 5$ V
Momentary current (20 ms, 0.1 Hz)		0 ... 2000 mA
Operating current	$I_L$	5 ... 200 mA
Off-state current	$I_r$	typ. 0.7 mA
Time delay before availability	$t_v$	$\leq 80$ ms
Switching state indicator		LED, yellow

### Standard conformity

Standards	IEC / EN 60947-5-2:2004
-----------	-------------------------


### Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
---------------------	--------------------------------


### Mechanical specifications

Housing material	Stainless steel
Sensing face	PBT
Degree of protection	IP67


## Dimensions



## Electrical Connection



## Pinout





Wire colors

1		BU	(blue)
2		BN	(brown)
4		GN/YE	(green/yellow)

Release date: 2016-06-02 11:57 Date of issue: 2016-06-02 186772\_eng.xml