


Dimensions



Model number


VAZ-T1-FK-V1R


Splitter box AS-Interface to 1x M12 round connector

Features

- Fixing component with captive screw
- Simple and fast mounting
- Gold plated contacts
- Housing made of fiberglass reinforced
- Immunity to vibration

Electrical connection





Technical data

Contacts

Housing

General	specifications
---------	----------------

Construction type		Socket, straight Flat cable terminal AS-Interface
Electrical specifications		
Rated operating voltage	U_e	≤ 35 V PELV (AS-Interface)
Rated operating current	l _e	≤ 4 A
Surge protection		U _e : Over voltage category III, safe isolated power supplies (PELV)
Ambient conditions		
Ambient temperature		-25 75 °C (-13 167 °F)
Storage temperature		-25 85 °C (-13 185 °F)
Pollution Degree		3
Mechanical specifications		
Protection degree		IP67 / IP68 / IP69k
Connection		Plug connection: M12 x 1 socket (V1)

Pin 1 AS-Interface+, Pin 3 AS-Interface-Material

AS-Interface flat cable: Insulation penetration technology

Mass	30 g
Tightening torque, fastening screws	1.65 Nm
O a service of the second and a service of all services.	

Compliance with standards and directives

Standard conformity	
Protection degree	EN 60529

CuSn / Au

PA 66-GF25 Ultramid