Accessories



CE

Model Number

PCV-USB-RS485-Converter Set

USB to RS 485 interface converter

Features

- Extension cable 0.8 m in scope of delivery
- Power supply for 95 230 V AC ٠
- For RS485 •

Technical data

PCV-USB-RS485-Converter Set

Indicators/operating means		
Operation indicator		LED red
Data flow indicator		LED yellow and LED green
Electrical specifications		
Operating voltage	UB	via USB
Interface 1		
Connection of		PC
Interface type		USB
Interface 2		
Connection of		Read head
Interface type		RS-422 / RS-485
Transfer rate		up to 921.6 kBit/s
Mechanical specifications		
Connection type		Screw terminals for 0.14 0.34 mm ² 9-pin Sub-D connector USB-Male Connector Typ B
Dimensions		70 mm x 67 mm x 22 mm
General information		
Scope of delivery		USB connection cable 800 mm
		24 V power supply and V19 cordset USB/RS-485 converter
Compliance with standards and directives		
Standard conformity		
Standards		EN 60947-5-2:2007 IEC 60947-5-2:2007

