



Model Number

PCV-KBL-V19-STR-USB

USB cable unit with power supply

Features

- Power supply for 95 - 230 V AC
- For SSI interface
- For PROFIBUS DP
- For CANopen
- For PROFINET
- For EtherNet/IP

Technical data

Electrical specifications

Operating voltage	U_B	95 ... 230 V AC, 40 ... 60 Hz
Output voltage		24 V DC
Output rated operating current		max. 1 A

Interface 1

Connection of	PC
Interface type	USB

Interface 2

Connection of	Read head
Interface type	USB

Mechanical specifications

Connection type	Female connector M12 x 1 , 8-pin USB-Male Connector Typ A (Standard)
-----------------	---

General information

Scope of delivery	Power supply USB cable unit
-------------------	-----------------------------

Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007