



Model Number

PGV33M-CB19-YE

PGV color-tape yellow

Features

- Self-adhesive mounting
- High mechanical stability

Technical data

General specifications

Length	33 m
Width	19 mm
External diameter	80 mm
Inside diameter	25 mm (role core)
Color	yellow

Ambient conditions

Operating temperature	-5 ... 70 °C (23 ... 158 °F)
Storage temperature	12 ... 25 °C (53.6 ... 77 °F)
Installation temperature	0 ... 40 °C (32 ... 104 °F)
Environmental resistance	UV radiation Humidity

Mechanical specifications

Material thickness	130 µm
Material	PVC
Thermal expansion coefficient	180 %
Tensile strength	28 N/cm
Adhesive strength	Average values (FTM2) Steel : 2.4 N / 10 mm Self : 2.1 N / 25 mm