



Model Number

OHV-BAT-CHARGER

Charger for OHV-BAT

Function

The OHV-BAT-CHARGER offers four slots for charging OHV-BAT-type lithium ion batteries. Each slot has its own status LED.

Technical data

Indicators/operating means

Operation indicator 4 green LEDs: charging indicator

Electrical specifications

Operating voltage U_B 5 V DC

Operating current I_B max. 1.2 A

Output

Output rated operating current 400 ... 1200 mA

Output voltage 5 V DC pulsing

Ambient conditions

Ambient temperature -20 ... 55 °C (-4 ... 131 °F)

Storage temperature -30 ... 65 °C (-22 ... 149 °F)

Mechanical specifications

Connection Supply voltage: 5.5 mm hollow socket

Mass approx. 245 g

Dimensions 138 mm x 89 mm x 60 mm