



## Code tape

PXV000004M-CA25-000000

- High chemical resistance
- Low weight
- Self-adhesive mounting
- High temperature resistance
- High mechanical stability

Data Matrix code tape

## Dimensions



## Technical Data

General specifications	
Start position	0 m
Length	4 m
Width	25 mm (1 row version)
External diameter	max. 180 mm (with max. code tape length of 100 m)
Inside diameter	76 mm ( role core )
Ambient conditions	
Operating temperature	-40 ... 100 °C (-40 ... 212 °F)
Installation temperature	10 ... 40 °C (50 ... 104 °F)
Environmental resistance	UV radiation Humidity Salt spray (150 h / 5%)
Chemical resistance	Oils Grease Fuels Aliphatic solvents Weak acids
Mechanical specifications	
Material thickness	150 µm
Material	polyester laminate
Surface	polyester , matte
Mass	6.3 g / m

Release date: 2023-06-22 Date of issue: 2023-06-22 Filename: 299652-100006\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

**PF** PEPPERL+FUCHS

## Technical Data

Tensile strength	≥ 150 N
Manufacturing tolerance	± 1 mm/m
Adhesive	Acrylate-based adhesive ; curing 72 h
Adhesive strength	Average values (FTM2) Aluminum : 24 N / 25 mm High grade stainless steel : 25 N / 25 mm ABS : 22 N / 25 mm PP : 18 N / 25 mm HD-PE : 12 N / 25 mm LD-PE : 12 N / 25 mm
Note	Max. code tape length of 100 m per roll

## Type Code

### Structure of the type code (Ordering information)

<b>P</b>	<b>X</b>	<b>V</b>	(1)	(1)	(1)	(1)	(1)	(1)	<b>M</b>	-	<b>C</b>	<b>A</b>	<b>2</b>	<b>5</b>	-	(2)	(2)	(2)	(2)	(2)	(2)
----------	----------	----------	-----	-----	-----	-----	-----	-----	----------	---	----------	----------	----------	----------	---	-----	-----	-----	-----	-----	-----

<b>PXV</b>	<b>Sensor Type</b>
PXV	Data Matrix positioning system (PXV)

<b>(1) (1) (1) (1) (1) (1)</b>	<b>Length of the code tape</b>
1 ... 100000	Total length of the code tape in m

<b>M</b>	<b>Length unit</b>
M	Meter

<b>CA</b>	<b>Code type</b>
C	Data Matrix ECC200, Symbol size 12x12
A	Absolute tape

<b>25</b>	<b>Width of the code tape</b>
25	25 mm

<b>(2) (2) (2) (2) (2) (2)</b>	<b>Start position</b>
0 ... 099999	Starting position of the code tape in m

## Accessories

	<b>PGV25M-CD160-CLEAR</b>	Protective laminate for PGV code tape
	<b>PGV25M-CD100-CLEAR</b>	Protective laminate for PGV code tape