


Measuring wheel

ACC-MW-GL-POL-300D1012

- Plastic coating
- 300 mm circumference

Measuring wheel for shaft diameter 10 mm

Dimensions



Technical Data

Ambient conditions	
Operating temperature	-30 ... 80 °C (-22 ... 176 °F)
Mechanical specifications	
Surface	smooth plastic Polyurethane
Diameter	D = 95.5 mm
Circumference	300 mm
Width	12 mm
Shaft diameter	d = 10 mm
Mass	110 g
Moment of inertia	1330 gcm²
General information	
Note	recommended contact pressure: 15 N

Release date: 2026-10-02 Date of issue: 2026-10-02 Filename: 311819_eng.pdf