



Tablet computer



Tab-Ex02-DZ2-WWANSRB-ANDCN00..

- Replaceable SIM
- Global certificates - a common platform
- Wireless connections such as WWAN, 4G LTE, WLAN, etc.
- Camera (front and main/optional)
- 8 MP camera with built-in flash on the main screen
- 5 MP front camera
- Comprehensive security thanks to Samsung KNOX
- Accessories and peripheral devices allow a wider range of applications
- Suitable for use with gloves
- NFC technology for wireless applications
- GPS
- Latest available Android version for this device

Tab-Ex 02 DZ2 (DIV 2 & Zone 2/22), latest available Android firmware release, WWAN (LTE) incl. WiFi, with camera, version for Serbia

Technical Data

Hardware	
Processor	Exynos 7 Octa, 1.6 GHz Octa-core (Cortex®-A53)
Working memory	RAM 3 GByte
Camera	
Front camera	5 MP
Main camera	8 MP Autofocus
Video recording resolution	Full HD (1920 x 1080 pixels) @ 30 fps
Internal data memory	16 GByte
Sensors	Acceleration sensor, proximity and ambient light sensor, gyroscope, geomagnetic, Hall sensor, facial recognition
Indicators/operating means	
Display	Can be operated while wearing gloves
Touchscreen technology	Capacitive multitouch
Type	TFT, LCD
Screen diagonal	20.31 cm
Resolution	1280 x 800 (WXGA)
Brightness	480 nit
Colors	16 Mio.
Electrical specifications	
Battery type	Li-Ion battery 16.91 WH 3.8 V 4450 mAh
Operating duration	up to 11 h
Communication	
Mobile standard	LTE Cat. 6 (300 Mbps)
2G	GSM 850 MHz, GSM 900 MHz, DCS 1800 MHz, PCS 1900 MHz
3G	UMTS band: B1 (2100), B2 (1900), B4 (AWS), B5 (850), B8 (900)
4G	LTE band: B1 (2100), B2 (1900), B3 (1800), B4 (AWS), B5 (850), B7 (2600), B8 (900), B17 (700), B20 (800), B28 (700)
WLAN	802.11 a/b/g/n/ac (2.4 GHz + 5 GHz)
Bluetooth	Bluetooth® 4.2
GPS sensor	GPS, Glonass, Beidou








Release date: 2020-12-09 Date of issue: 2020-12-09 Filename: 480982-100367_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".




Technical Data

USB	USB 2.0
Connections	Wi-Fi Direct, NFC, ANT+
SIM card	1 x Nano SIM (4FF)
Software	
Operating system	Android™
Languages	Deutsch English (default)
Safety	Samsung KNOX 3.2
SMS/MMS	yes
Ambient conditions	
Ambient temperature	-20 ... 55 °C (-4 ... 131 °F)
Mechanical specifications	
Degree of protection	IP64
Mass	WWAN 579 g
Dimensions	H x W x D 127.6 mm x 247.7 mm x 9.9 mm
Data for application in connection with hazardous areas	
ATEX approval	
Certificate of conformity	EPS 18 ATEX 1 055 X
ATEX marking	Ⓜ II 3G Ex ic IIC T5 Gc Ⓜ II 3D Ex ic IIIB T100 °C Dc
International approvals	
IECEx approval	
IECEx certificate	IECEx EPS 18.0029X
IECEx marking	Ex ic IIC T5 Gc Ex ic IIIB T100 °C Dc
Approved for	Serbia
General information	
Scope of delivery	Tab-Ex® 02 Battery Ex-protective cover S Pen USB cable Travel charger Documentation

Accessories

	DC T01 X2 (EU / UK / AUS / NZ)	Desktop charging station, 5-slot, for Tab-Ex® 01 D2, Z2, DZ2 and Tab-Ex® 02 DZ2
	DC T01 X2 (US)	Desktop charging station, 5-slot, for Tab-Ex® 01 D2, Z2, DZ2 and Tab-Ex® 02 DZ2
	LC T01 X2	Leather case for Tab-Ex® 01 and 02 D2/Z2/DZ2
	CH T01 X2	Chest strap carrying system
	BP T01 X2	Battery pack
	BC T01	Belt loop with carabiner
	S Pen Tips u. Tweezers	Tip ends and tip removal tweezers for ST T02 X2

Accessories

	PC T02	USB connection cable
	Samsung EVO PLUS microSDXC	256 GB microSD card for Tab-Ex® 02
	HM-MT-BT-EX-010041	Interface for wireless communication between PC host and HART field devices

Release date: 2020-12-09 Date of issue: 2020-12-09 Filename: 480982-100367_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**