



# Remote Speaker Microphone

## RSM-EX01SNG-Z1EUR-1EWN...ST



- Extremely long operating times with high voice volume – Up to 78 hours
- Outstanding volume and sound performance – Up to 103 dB
- Good operability, even with gloves
- Lone worker ready (with Red Button)
- Additional multi-functional buttons and a dedicated SOS button
- 2200 mAh Li-ion battery pack for a long operating time
- Linguistic feedback when changing individual modes
- Magnetic charging cable and optional charging cradle
- IoT Ready: "Custom Service Load" allows individual button settings for sending custom commands to servers and other IoT switches - e.g. to open a gate (only for Ex-Handy 10 Series)

RSM-Ex 01, wired, Zone 1, straight 3.5 mm plug for Smart-Ex 02 & Ex-Handy 10, with Red Button, version for Europe



### Technical Data

<b>Indicators/operating means</b>	
Key	PTT button operable with thick gloves Front-facing multi-function button Volume up / down with Red Button
<b>Audio data</b>	
Sound level	up to 103 dB
<b>Electrical specifications</b>	
Battery type	Li-Ion battery 2200 mAh
Operating duration	Stand-by time: approx. 80 h Actual use/operating time depending on use and set sound level (See table "Run times")
<b>Communication</b>	
NFC	yes
<b>Ambient conditions</b>	
Ambient temperature	-20 ... 55 °C (-4 ... 131 °F)
<b>Mechanical specifications</b>	
Degree of protection	IP 64 following EN/IEC 60079-0 (ATEX/ IECEx) IP 65 / 67 following EN/IEC 60529 (industrial standard)
Connection	Socket, 3.5 mm, for headset
Connector	3.5 mm, 4-pin, straight, Next Generation (Smart-Ex 02 / Ex-Handy 10)
Cable	coiled
<b>Data for application in connection with hazardous areas</b>	
ATEX approval	
ATEX certificate	IBExU18ATEX1124 X
ATEX marking	⊕ II 2G Ex ib IIC T4 Gb ⊕ II 2D Ex ib IIIC T135°C Db IP64 ⊕ I M2 Ex ib I Mb
<b>International approvals</b>	
IECEX approval	
IECEX certificate	IECEX IBE 18.0016X
IECEX marking	Ex ib IIC T4 Gb Ex ib IIIC T135°C Db IP64 Ex ib I Mb
Approved for	Europe
<b>General information</b>	

Release date: 2020-12-10 Date of issue: 2020-12-10 Filename: 480984-100018\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com








Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com



## Technical Data

Scope of delivery	RSM-Ex Battery Charging cable Charger Safety instructions Documentation
-------------------	--

## Accessories

	<b>EXT-C2LCOIL CLIP2LOOP COIL</b>	Clip2Loop Coil Tether
	<b>MINI QD LOOP</b>	Mini QD Loop
	<b>RL ID01</b>	Retractable Lanyard
	<b>CC S01-R</b>	Car charger
	<b>DS RSM 01</b>	Docking station
	<b>TC S02 Travel Charger</b>	Travel charger
	<b>Charging Cable RSM</b>	USB Charging Cable

Release date: 2020-12-10 Date of issue: 2020-12-10 Filename: 480984-100018\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

## Operation

### Run times\*\*

Use time in % with typical user profiles speak/hear/standby	Noisy areas with sound level above 100 dB	Noisy areas with sound level between 84 and 100 dB	Noisy areas with sound level up to 84 dB
5 / 5 / 90	-> 55 h	-> 72 h	-> 72 h
25 / 25 / 50	-> 28 h	-> 70 h	-> 71 h
50 / 50 / 0	-> 17 h	-> 67 h	-> 69 h
	Highest noise level (8/8)*	Very high noise level (4/8)*	High noise level (2/8)*
*There are 8 different volume levels possible. **determined runtimes on the Smart-Ex 01 based on RSM-Ex 01 software version V 16			